


Product description	<b>M8 Male cable connector, Contacts: 4, shielded, moulded on the cable, IP67, Profinet/Ethernet CAT5e, PUR, green, 4 x AWG 22, 2 m</b>
Area	<b>M8-D</b>
Coding	<b>D-coded</b>
Series	<b>818</b>
Part no.	<b>77 5429 0000 50704-0200</b>


### Illustration



### Scale drawing



### Contact arrangement (Plug-in side)



### Cable length tolerance

<i>cable length</i>	<i>tolerance</i>
≥ 0,10 m	+ 0,03 m
≥ 0,20 m	+ 0,04 m
≥ 0,50 m	+ 0,07 m
≥ 1,00 m	+ 0,10 m
≥ 2,00 m	+ 0,15 m
≥ 5,00 m	+ 0,20 m
≥ 10,0 m	+ 0,25 m
≥ 20,0 m	+ 0,35 m

### Technical data

#### General features

Part no.	<b>77 5429 0000 50704-0200</b>
Connector design	Male cable connector
Type standard	DIN EN 61076-2-114
Coding	D-coded
Cable length	2 m (Standard 2 m and 5 m. Other lengths are available on request.)
Version	Connector pin straight
Connector locking system	M8x1
Termination	moulded on the cable
Degree of protection	IP67
Connection cross-section	0.34 mm <sup>2</sup> / AWG 22
Temperature range from/to	-25 °C / 85 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	266
Customs tariff number	85444290

Product description	<b>M8 Male cable connector, Contacts: 4, shielded, moulded on the cable, IP67, Profinet/Ethernet CAT5e, PUR, green, 4 x AWG 22, 2 m</b>
Area	<b>M8-D</b>
Coding	<b>D-coded</b>
Series	<b>818</b>
Part no.	<b>77 5429 0000 50704-0200</b>

Country of Origin	DE
-------------------	----

### Electrical parameters

Rated voltage	63 V
Rated impulse voltage	1500 V
Rated current	4.0 A
Insulation resistance	> 10 <sup>8</sup> Ω
Pollution degree	3
Overvoltage category	II
Insulating material group	I
EMC compliance	shielded
Shield connection	Shield on the threaded ring

### Material

Housing material	PUR
Contact body material	PUR black
Contact material	CuZn (brass)
Contact plating	Au (gold)
Locking material	CuZn (brass)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	4182f23a-980d-4022-8f60-cdde6dd0bb79

### Cable data - Structure of the cable

Cable type	Profinet/Ethernet CAT5e
Cable diameter	6.7 mm
Cross section	4 x AWG 22
Sheath material	PUR
Single-lead insulation	Polyolefin
Cable color	green

### Cable data - Electrical properties

Conductor resistance	55 Ω/Km (20°C)
----------------------	----------------

### Cable data - Mechanical properties

Bending radius, fixed cable	≥ 5 x Ø
Bending radius, moving cable	≥ 15 x Ø
Bending cycles	2 million
Permitted acceleration	max. 2 m/s <sup>2</sup>
Travel distance, horizontal	max. 5 m
Travel distance, vertical	max. 5 m
Travel speed	200 m/min

Product description	<b>M8 Male cable connector, Contacts: 4, shielded, moulded on the cable, IP67, Profinet/Ethernet CAT5e, PUR, green, 4 x AWG 22, 2 m</b>
Area	<b>M8-D</b>
Coding	<b>D-coded</b>
Series	<b>818</b>
Part no.	<b>77 5429 0000 50704-0200</b>

### Cable data - Thermal properties

Temperature range cable in move from/to	-20 °C / 60 °C
Temperature range cable fixed from/to	-40 °C / 80 °C

### Cable data - Other features

Halogen free	yes
--------------	-----

### Classifications

eCl@ss 11.1	27-06-03-11
ETIM 9.0	EC002638

### Declarations of conformity

RoHS Directive	2011/65/EU (EN 50581:2012)
----------------	----------------------------

Product description	<b>M8 Male cable connector, Contacts: 4, shielded, moulded on the cable, IP67, Profinet/Ethernet CAT5e, PUR, green, 4 x AWG 22, 2 m</b>
Area	<b>M8-D</b>
Coding	<b>D-coded</b>
Series	<b>818</b>
Part no.	<b>77 5429 0000 50704-0200</b>

## General Disclaim Notice

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

To protect against unintentional opening of the connector, the thread between the housing and the connector head must be secured with a suitable cyanoacrylate adhesive when used in circuits with voltages dangerous to the touch. This does not apply to connectors used in SELV and PELV circuits according to IEC 61140 (EN 61140, VDE 0140-1).

Connectors which are used in circuits with voltages dangerous to the touch may only be installed and used by, or under the supervision of, persons with electrical engineering training, taking into account the applicable regulations and standards.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP67 and IP68 are not suitable for use under water. When used outdoors, the plug connectors must be protected separately against corrosion. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

Please observe the pollution degree and the overvoltage category. For further information, please refer to the download center "Technical Information".

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 40 cNm).