



ENGLISH

Datasheet

RS Article:1835723


RS PRO Lithium Thionyl Chloride Battery



► MODEL NO.: ER17335

■ SPECIFICATION: ($23 \pm 2^\circ\text{C}$)

Nominal capacity (2mA ~ 2V):	2.1 A h
Rated voltage:	3.6 V
Max constant current of discharge:	100 mA
Max discharge current (pulse):	200mA
Weight:	21 g
Operating temperature range:	$-55 \sim 85^\circ\text{C}$



S: Standard termination

Notes:

Dimension: mm

Special terminations can be Made as requested.


T: Solder tabs

P: Axial pins


Warning

- Fire, explosion, and burn hazard.
- Do not recharge, short circuit, over discharge, crush, disassemble, heat above 100 incinerate.
- Do not use the battery beyond permitted temperature.
- Do not place in a packet.


■ Discharge characteristics at $23 \pm 2^\circ\text{C}$



■ Capacity VS. Current



■ Voltage VS. Temperature



Benefits:

- High Energy density
- High Voltage stable during most of applications lifetime
- Wide range of operating temperature (-55°C +85°C)
- Long storage life
- Low self-discharge rate 1% per year at 20°C
- Long Shelf life due to its full-sealing structure: It can be stored for more than 15 years.

Main application

- Intelligent Instrument and meter
- Memory and standby power
- Alarms and security devices
- Automotive electronics
- Electronic toll collection
- Military devices

Drawing detail:

