

247.3296**FLUSH MOUNTING APPLIANCE
INLET**32A 3P+E 6h 380-415V 60Hz 50Hz
70X87MM Screw terminals

* Product image may be indicative



EN IEC 60309-1 (2022)

EN IEC 60309-2 (2022)

Low voltage direct. 2014/35/EU

■ GENERAL CHARACTERISTICS

Commercial Series	EUREKA Series
Synthetical description	FLUSH MOUNTING APPLIANCE INLET
Description	
The EUREKA Series flush mounting appliance inlet, engineered for high-performance electrical applications, operates at a rated voltage of 380-415V and a rated current of 32A. It features a 3P+E configuration with a 6h hour position, accommodating both 50Hz and 60Hz working frequencies. This inlet provides robust protection with an IP66/IP67 rating, effectively guarding against dust and water ingress. Designed with screw terminals, it ensures secure and efficient connections. Available in a 90° angled outlet type, this appliance inlet is a reliable solution for demanding industrial environments.	
Mounting version	FLUSH/SURFACE MOUNTING

■ TECHNICAL CHARACTERISTICS

Rated current	32A
Poles	3P+E
Hour position	6h
Rated voltage	380-415V
Working frequency	60Hz
	50Hz
Terminals	Screw terminals

■ PHYSICAL CHARACTERISTICS

Mounting version	FLUSH/SURFACE MOUNTING
Colour	RED
Material	THERMOPLASTIC
Protection degree	Watertight
Protection degree IP	IP66/IP67
Protection degree IK	IK07
Types of available outlets	90° ANGLED
Contact material	CuZn (brass)
Surface treatment contacts	Nickel-plated
Cable entry	PG 16

■ DIMENSIONAL CHARACTERISTICS

Flange	70X87MM
--------	---------

■ DOWNLOAD

[Technical drawing \[PDF\]](#)
[Technical drawing \[STP\]](#)
[Technical drawing \[DWG\]](#)