

# HC-M-01P-CT-M-70 - Contact insert module



1687651

<https://www.phoenixcontact.com/gb/products/1687651>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert module, number of positions: 1, power contacts: 1, control contacts: 0, Pin, Crimp connection, 1000 V, 200 A, 16 mm<sup>2</sup> ... 70 mm<sup>2</sup>, application: Power, without crimp contacts

## Commercial data

Item number	1687651
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AF7ACE
Product key	AF7ACE
GTIN	4067923247314
Weight per piece (including packing)	23.7 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

# HC-M-01P-CT-M-70 - Contact insert module



1687651

<https://www.phoenixcontact.com/gb/products/1687651>

## Technical data

### Notes

General	Order crimp contacts separately
General	Order crimp contacts separately

### Mounting

Assembly note	To ensure correct use, installation in housing with IP54 protection or better is required
---------------	---

### Product properties

Product type	Modular contact insert
Series	HC-M-01
Application	Power
Number of positions	1
Connection profile	1
Number of module slots	2
No. of power contacts	1
No. of control contacts	0
Contact material type	turned

### Connection data

#### Connection technology

Connection technology	Crimp connection
-----------------------	------------------

#### Conductor connection

Conductor cross section	16 mm <sup>2</sup> ... 70 mm <sup>2</sup> (The cross section specification refers to the geometric cross section of the cable used)
Connection cross section AWG	6 ... 2/0 (The cross section specification refers to the geometric cross section of the cable used)

### Dimensions

Width	34 mm
Height	56.2 mm
Length	29.5 mm

#### Mechanical characteristics

Contact diameter	9.5 mm
------------------	--------

### Electrical properties

Rated voltage (III/3)	1000 V
Rated surge voltage	8 kV
Rated current	200 A

### Mechanical properties

# HC-M-01P-CT-M-70 - Contact insert module



1687651

<https://www.phoenixcontact.com/gb/products/1687651>

## Mechanical data

Insertion/withdrawal cycles	≥ 500
-----------------------------	-------

## Material specifications

Contact material	Copper alloy
Contact surface material	Ag
Contact carrier material	PC
Standards/regulations	PC


## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

## Drawings

Diagram



Derating diagram

# HC-M-01P-CT-M-70 - Contact insert module



1687651

<https://www.phoenixcontact.com/gb/products/1687651>

## Classifications

### ECLASS

ECLASS-13.0	27440217
ECLASS-15.0	27440217

### ETIM

ETIM 9.0	EC000438
----------	----------

# HC-M-01P-CT-M-70 - Contact insert module



1687651

<https://www.phoenixcontact.com/gb/products/1687651>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)