




Jun.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved. In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C	STORAGE TEMPERATURE RANGE	-- °C TO -- °C	
	VOLTAGE	300 V AC	OPERATING HUMIDITY RANGE	-- % TO -- %	
	CURRENT	2 A	APPLICABLE CABLE		
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.			X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).		20 mΩ MAX.	X	-
INSULATION RESISTANCE	100 V DC.		10 ⁶ MΩ MIN.	X	-
VOLTAGE PROOF	1000 V AC FOR 1 min.		NO FLASHOVER OR BREAKDOWN.	X	-
MECHANICAL CHARACTERISTICS					
INSERTION AND WITHDRAWAL FORCES	MEASURED BY APPLICABLE CONNECTOR.		INSERTION FORCE: 0.98 N/PIN MAX. EXTRACTION FORCE: 0.156 N/PIN MIN.	X	-
MECHANICAL OPERATION	500 TIMES INSERTIONS AND EXTRACTIONS.		1) CONTACT RESISTANCE: 20 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	-
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, - m/s ² AT 2 h, IN 3 DIRECTIONS.		1) NO ELECTRICAL DISCONTINUITY OF 1 μs. 2) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	-
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIME IN 3 DIRECTION.			X	-
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.		1) CONTACT RESISTANCE: 20 mΩ MAX. 2) INSULATION RESISTANCE:	X	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -55→15 TO 35→125→15 TO 35°C TIME 30→10 TO 15 →30→10 TO 15min. UNDER 5 CYCLES.		10 ⁶ MΩ MIN. 3) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	-
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.		1) CONTACT RESISTANCE: 20 mΩ MAX. 2) NO HEAVY CORROSION.	X	-
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
					
REMARK			APPROVED	KI.AKIYAMA	05.07.20
			CHECKED	SI.TOMIOKA	05.07.20
			DESIGNED	HT.SUGIMURA	05.07.20
Unless otherwise specified, refer to MIL-STD-1344.			DRAWN	HM.SAITO	05.07.19
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.	ELC4-154678-01	
	SPECIFICATION SHEET		PART NO.	PCN10C-**S-2. 54DSA (72)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.		1/1