

Specifications for BMP71 PermaSleeve Wire Marker Sleeves

| | |
|--------------------------------------|--|
| Article No. | 114995 |
| Brady Material No. | B-342 |
| Material Type | Heat-shrink Polyolefin Sleeve |
| Colour | White |
| Finish | Matt |
| Order Reference | M71-94-1-342 |
| Printer Compatibility | BMP71 |
| Size - Height (mm) | 4.62 |
| Size - Width (mm) | 25.78 |
| Additional Information | Heat-shrinkable;Self-Extinguishing |
| Total Qty per Pack | 100 Sleeve(s) / Box |
| Wire Gauge | 28 to 18 |
| Approval/Compliance | SAE-AMS-DTL-23053/5 C (Class 1); SAE-AS-81531; MIL-STD-202 method 215K; UL224 |
| Ribbon Series | M71-R4300 |
| Application | Wire & Cable Marking |
| Industry | Aerospace;Data & Telecommunications;Defence;Electrical;Mass Transit |
| Description | PermaSleeve markers provide a wire marking solution that combines speed, ease of use, and permanence to create long-lasting, high quality identification. These Sleeves are self-extinguishing and meet the requirements of SAE AMS-DTL-23053/5 Class 1, SAE-AS-8153, MIL-STD-202 method 215K and is UL224 recognised. CSA acceptance pending. |
| Max. Characters per Line | 22 |
| Max. Lines of Text | 1 |
| Max. Service Temp. °C | 130 |
| Max. Wire/Cable Diameter (mm) | 2.03 |
| Min. Service | -70 |

| | |
|--------------------------------------|------------------------|
| Temp. °C | |
| Min. Wire/Cable Diameter (mm) | 0.58 |
| Printable Sides | Single-sided Printable |
| Shape | Rectangle |
| Shrink Ratio | 3:1 |