

PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Glue guns and accessories
Catalogue number	6215, 6215A, 6216, 6218, 6219
Date	20/02/2009

Range Description

Glue guns and accessories

Features

6215/6215A

- Professional quality glue gun
- 80w heater for fast heating and improved glue flow
- CE approved
- Molded trigger advance for precise control during glue application
- Safety heat insulated nozzle
- Detachable wire stand
- Max glue output, 21g/Min
- Supplied with two 100mm x 11mm glue sticks



6215 (UK Plug)



6215A (Euro plug)

6216

- 6215A (Euro plug) glue gun complete with 12x200mm glue sticks in a storage/carrying case



6216

6218

- All purpose glue sticks
- 100mm long
- Packs of 6 or 25



6218

6219

- All purpose glue sticks
- 200mm long
- Packs of 25 or 125



6219

Item number	Item Description	EAN No	Commodity code	Carton Qty
T6215	Glue Gun 80w UK Plug	5013969027808	82055990	6
T6215A	Glue Gun 80w Euro Plug	5013969027815	82055990	6
T6216	Glue Gun Kit 80w Euro Plug	5013969978971	82055990	1
T6218 06	All purpose Glue sticks 100mm Pack of 6	5013969031416	35061000	6
T6218 25	All Purpose Glue Sticks 100mm Pack of 25	5013969031423	35061000	6
T6219 025	All purpose Glue sticks 200mm Pack of 25	5013969979688	35061000	1
T6219 125	All Purpose Glue Sticks 200mm Pack of 125	5013969979695	35061000	1

Technical product information	Glue melt temperature – 120 degrees Centigrade Maximum heater element temperature – 193 degrees Centigrade
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	These products are fully WEEE and RoHS compliant
Material safety data	See appendix 1
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Taiwan

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T6215	210	35	70	389	185	50	290	434
T6215A	210	35	70	374	185	50	290	419
T6216	330	45	240	1120	330	45	240	1155
T6218 06	35	30	100	60	80	30	180	78
T6218 25	100	30	100	244	100	30	100	248
T6219 025	150	25	200	484	150	25	200	492
T6219 125	245	70	200	2420	245	70	200	2432

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T6215	295	295	190	2930		
T6215A	295	295	190	2840		
T6216	-	-	-	-		
T6218 06	100	245	85	530		
T6218 25	105	315	65	1565		
T6219 025	-	-	-	-		
T6219 125	-	-	-	-		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T6215	35	Blister	10	Backing card			326	Box
T6215A	35	Blister	10	Backing card			326	Box
T6216	5	Cover	30	Sleeve			-	-
T6218 06	8	Blister	10	Backing card			70	Box
T6218 25	4	Bag	-	-			77	Box
T6219 025	8	Bag	-	-			-	-
T6219 125	12	Bag	-	-			-	-

1. Identification of the substance / preparation and of the company

Product: T6218 Glue Sticks

Manufacturer: Carl Kammerling International Ltd

C.K House, Pwllheli. LL53 5LH

Tel: +44 (0) 1758 701070

Fax: +44 (0) 1758 704777

Emergency Tel: +44 (0) 1758 701070

Type : Hotmelt based on EVA-copolymer.

Intended use:

Hotmelt Adhesive.

2. Composition/information on ingredients:

EVA-copolymer / Synthetic resin / Wax and Stabilizer

The product does not contain any substances presenting a health hazard within the meaning of the Danish and EC regulations.

3. Hazards identification:

Gases formed at high temperatures may irritate the eyes and the respiratory tract.

As a liquid, the material may cause serious burns.

4. First aid measures:

General:

In all cases of doubt, seek medical attention.

Inhalation:

In case of exposure to gases formed at high temperatures remove affected person from area. Fresh air and rest. Seek medical advice if discomfort persists.

Eye contact:

Remove contact lenses. After separating the eyelids flush with copious amounts of water, at least 10 min. seek medical advice.

Skin contact (Burns):

Rinse with cold water until the pain stops. If medical advice is necessary, rinse until doctor takes over treatment.

Ingestion:

Do not induce vomiting. If vomiting occurs, hold head low so stomach content does not enter the lungs. Seek immediate medical advice.

5. Fire fighting measures:

Extinguishing media: Foam, CO2, dry chemical, water spray

Fire will produce dense black smoke containing products of combustion.

Decomposition products may be a hazard to health. Appropriate self-containing breathing apparatus may be required.

Hazardous Combustion Products : carbon dioxide, carbon monoxide

6. Accidental release measures:

See protective measures listed in section 8.

In case of spills allow to cool and sweep up. Hold waste for disposal according to local regulations (see section 13).

7. Handling and storage:

Handling:

Avoid skin and eye contact with melted product. Avoid inhalation of warm gases. For personal protection see section 8.

Storage:

Store product in tightly closed container in a dry place. Keep out of the reach of children.

8. Exposure controls / personal protection:

Technical facility design: provide adequate ventilation. Preferably use an extractor hood over the location used for the melted product.

Personal protection:

Respiratory protective equipment:

Avoid breathing warm gases.

Hand protection:

Use protective gloves when handling the melted product.

Eye protection:

Use if necessary suitable eye protection when near the melted product.

Skin protection:

Use suitable work clothes when near the melted product.

9. Physical and chemical properties:

Physical state: 20°: Solid
120°: Liquid
Colour: clear white
Flash point: >200°
Viscosity: 13000cps / 170°
PH: -
Density, g/ml: -
Water solubility: Insoluble
Weight% organic solvents: 0
Product, Flammable liquid of class: None

10. Stability and reactivity:

If exposed to high temperatures (>200°), hazardous decomposition products may be produced.

Copyright Carl Kammerling International Ltd

11.Toxicological information:**Properties injurious to health:**

Gases formed at high temperatures may irritate the eyes and the respiratory tract.

12.Ecological information:

Do not release product into the environment or the drains.

13.Disposal considerations:

The product should be disposed of in accordance with national or local regulations.

14.Transport information:

The product is not classified as dangerous for carriage.

15.Regulatory information:

This product has been classified in accordance with Danish and EC Directives on Hazardous Materials.

Hazard symbol: The product is not classified as dangerous. No classification and labeling.

Application restrictions: -

16.Other information:

The information contained in this safety data sheet is based on the present state of knowledge and current EC and Danish legislation.

The product should not be used for purposes other than those shown in section 1.

As the specific conditions of use of the product are outside the suppliers control, the user is responsible for ensuring that the requirements of relevant legislation are complied with.

The information in this safety data sheet provides guidance on health, safety and environmental aspects of the product and should not be construed as any guarantee of technical particular or suitable for particular applications.

In case of medical attention, bring this safety data sheet.

4. Identification of the substance / preparation and of the company

Product: T6219 Glue Sticks

Manufacturer: Carl Kammerling International Ltd

C.K House, Pwllheli. LL53 5LH

Tel: +44 (0) 1758 701070

Fax: +44 (0) 1758 704777

Emergency Tel: +44 (0) 1758 701070

Type : Hotmelt based on EVA-copolymer.

Copyright Carl Kammerling International Ltd

Intended use:

Hotmelt Adhesive.

5. Composition/information on ingredients:

EVA-copolymer / Synthetic resin / Wax and Stabilizer

The product does not contain any substances presenting a health hazard within the meaning of the Danish and EC regulations.

6. Hazards identification:

Gases formed at high temperatures may irritate the eyes and the respiratory tract.

As a liquid, the material may cause serious burns.

4. First aid measures:**General:**

In all cases of doubt, seek medical attention.

Inhalation:

In case of exposure to gases formed at high temperatures remove affected person from area. Fresh air and rest. Seek medical advice if discomfort persists.

Eye contact:

Remove contact lenses. After separating the eyelids flush with copious amounts of water, at least 10 min. seek medical advice.

Skin contact (Burns):

Rinse with cold water until the pain stops. If medical advice is necessary, rinse until doctor takes over treatment.

Ingestion:

Do not induce vomiting. If vomiting occurs, hold head low so stomach content does not enter the lungs. Seek immediate medical advice.

11. Fire fighting measures:

Extinguishing media: Foam, CO₂, dry chemical, water spray

Fire will produce dense black smoke containing products of combustion. Decomposition products may be a hazard to health. Appropriate self-containing breathing apparatus may be required.

Hazardous Combustion Products : carbon dioxide, carbon monoxide

12. Accidental release measures:

See protective measures listed in section 8.

In case of spills allow to cool and sweep up. Hold waste for disposal according to local regulations (see section 13).

13. Handling and storage:**Handling:**

Copyright Carl Kammerling International Ltd

Avoid skin and eye contact with melted product. Avoid inhalation of warm gases. For personal protection see section 8.

Storage:

Store product in tightly closed container in a dry place. Keep out of the reach of children.

14. Exposure controls / personal protection:

Technical facility design: provide adequate ventilation. Preferably use an extractor hood over the location used for the melted product.

Personal protection:

Respiratory protective equipment:

Avoid breathing warm gases.

Hand protection:

Use protective gloves when handling the melted product.

Eye protection:

Use if necessary suitable eye protection when near the melted product.

Skin protection:

Use suitable work clothes when near the melted product.

15. Physical and chemical properties:

Physical state: 20°: Solid
120°: Liquid
Colour: clear white
Flash point: >200°
Viscosity: 13000cps / 170°
PH: -
Density, g/ml: -
Water solubility: Insoluble
Weight% organic solvents: 0
Product, Flammable liquid of class: None

16. Stability and reactivity:

If exposed to high temperatures (>200°), hazardous decomposition products may be produced.

11. Toxicological information:

Properties injurious to health:

Gases formed at high temperatures may irritate the eyes and the respiratory tract.

12. Ecological information:

Do not release product into the environment or the drains.

13. Disposal considerations:

The product should be disposed of in accordance with national or local regulations.

14.Transport information:

The product is not classified as dangerous for carriage.

15.Regulatory information:

This product has been classified in accordance with Danish and EC Directives on Hazardous Materials.

Hazard symbol: The product is not classified as dangerous. No classification and labeling.

Application restrictions: -

16.Other information:

The information contained in this safety data sheet is based on the present state of knowledge and current EC and Danish legislation.

The product should not be used for purposes other than those shown in section 1.

As the specific conditions of use of the product are outside the suppliers control, the user is responsible for ensuring that the requirements of relevant legislation are complied with.

The information in this safety data sheet provides guidance on health, safety and environmental aspects of the product and should not be construed as any guarantee of technical particular or suitable for particular applications.

In case of medical attention, bring this safety data sheet.