




FAG

KHM88649-HM88610 [🔗](#)

Tapered roller bearing

Tapered roller bearings K-Series, in inch sizes, separable, adjusted or in pairs

Technical information



Your current product variant

Tolerance class	ABMA4	Class 4 (ANSI/ABMA 19.2:2013)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Quality level	Standard	
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	34.925 mm	Bore diameter
D	72.233 mm	Outside diameter
B	25.4 mm	Width, inner ring
C	19.842 mm	Width, outer ring
T	25.4 mm	Width, total
C _r	68,000 N	Basic dynamic load rating, radial
C _{0r}	91,000 N	Basic static load rating, radial
C _{ur}	11,200 N	Fatigue load limit, radial
n _G	10,000 1/min	Limiting speed
n _{gr}	7,100 1/min	Thermal speed rating
≈m	0.508 kg	Weight



Mounting dimensions

d _a max	41 mm	Maximum diameter of shaft shoulder
d _b min	46 mm	Minimum diameter of shaft shoulder
D _a min	57 mm	Minimum diameter of housing shoulder
D _a max	64 mm	Maximum diameter of housing shoulder
D _b min	68 mm	Minimum diameter of housing shoulder
C _a min	4 mm	Minimum axial space
C _b min	5.5 mm	Minimum axial space
r _a max	2.3 mm	Maximum fillet radius of shaft
r _b max	2.3 mm	Maximum fillet radius of housing

Dimensions

r _{1, 2} min	2.3 mm	Minimum chamfer dimension of inner ring back face
r _{3, 4} min	2.3 mm	Minimum chamfer dimension of outer ring back face
a	21 mm	Distance between the apexes of the pressure cones
d ₁	57.1 mm	Guidance rib diameter of inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0.55	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	1.1	Dynamic axial load factor
Y ₀	0.6	Static axial load factor



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed