Features

- PID Temperature Controller
- K Type Termocouple Input Type
- 4 Digits Display
- 230Vac Power Supply
- Selectable Heating or Cooling Function
- Process Output SSR (20mA@17Vdc)
- Alarm Output Relay (5A@250Vac)

RS PRO PID Temperature Control

RS Stock No:
874168



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Temperature Controller

Product Description

Digital PID and ON/OFF Temperature Control Device
K, NiCr-Ni IEC584.1 (ITS90) Input type (Scale: 0…999°C)
1X SSR Output, 20mA@17Vdc
1X Alarm Output, Relay (5A@250Vac)
4 Digits display
Applications Fields
- Machinery Manufacturing
- Panel Manufacturing:
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications

General Specifications

Supply Voltage and Power	230Vac 50/60Hz – 2,5A
Sensor Inputs	K, NiCr-Ni IEC584.1 (ITS90) (Scale: 0…999°C)
Output (Process)	1X SSR Output, 20mA@17Vdc
Output (Alarm)	1 Relay Output (5A@250Vac) at resistive Load
Accuracy	Scale ± %0.25

Mechanical Specifications

Dimension	77 mm x 35 mm 62,5 mm
Panel	IP65 at front, IP20 at rear
Max. Operating Temperature / Humidity	50°C / 90 % max. (None condensing)

Electrical Connection

