



P	LTR	DESCRIPTION	DATE	DWN	APVD
A		PRODUCTION RELEASE	03OCT2024	AK	BL
B		REVISED PER ECR-24-224301	29OCT2024	AK	BL
B1		REVISED PER ECN-25-313560	26MAR2025	GK	JW
B2		REVISED PER ECN-25-348637	14OCT2025	GK	JP

D




C

40P G12.5, TPA, FLIP-N-LOK




B

30P G12.5, TPA, FLIP-N-LOK



A

20P G12.5, TPA, FLIP-N-LOK



NOTES:

- 1 COMPATIBLE WITH:
 40P : 2395224-1
 20P : 2395224-2/-3
 30P : 2395224-4

2. ASSEMBLY INSTRUCTION: 408-160088

3 THIS PRODUCT HAS NOT COMPLETED QUALIFICATION TESTING

4 PRELIMINARY PART - NOT RELEASED FOR PRODUCTION

BLACK	THERMOPLASTIC	40.9	30	2395226-3	4 3
BLACK	THERMOPLASTIC	28.4	20	2395226-2	3
BLACK	THERMOPLASTIC	53.4	40	2395226-1	3
COLOR	MATERIAL	A	DESCRIPTION	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN G. KLINGER 02OCT2025	 TE Connectivity		
DIMENSIONS: mm		CHK E. WORKMAN 02OCT2025			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. POTERJOY 02OCT2025	NAME G12.5, TPA, FLIP-N-LOK		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 108-160822	RESTRICTED TO		
MATERIAL SEE TABLE		APPLICATION SPEC 114-106077	SIZE A3	CAGE CODE 00779	DRAWING NO G-2395226
FINISH SEE TABLE		WEIGHT -	SCALE 1:1 SHEET 1 OF 1 REV B2		
-		CUSTOMER DRAWING			