

# RANGE-LITE

Range-Lite is a compact twin spot lamp unit suitable for use in warehouse and factory spaces. The HV version can be wall or stanchion mounted.

- 20w TH lamp
- Projectors with unique adjustable knuckles for horizontal and vertical positioning
- Mild steel enclosure
- Non-maintained – 3 hour duration
- Model with time delay feature to support slow start mains luminaires



Specification	Self-contained
	<b>Electrical &amp; operational</b>
Input voltage	230-240Vac 50Hz
Duration	3 hours (non-maintained)
Battery	Sealed lead acid, 3-5 year design life
Charger & monitor	Pulse charger, with LED monitor
Recharge period	24 hours
Lamp	2 x 20w tungsten halogen. Circular PC lamp bodies with clear PC lenses
Lamp output	300 lumens (20w)per lamp
Lamp mounting	Two positions on top of enclosure
	<b>Construction &amp; installation</b>
Cable entry	20mm knockouts
Construction	Mild steel enclosure, with removable front panel
Environment	0 – 25° C
Ingress class	IP20
Dimensions hwd (mm)	214 x 260 x 62
Lamp dimensions:	Ø- 120mm, overall product height – 358mm
Weight (kg)	7.8
Product standards	Designed & manufactured to meet the standards of BSEN60598.2.22. CE marked
<b>To order:</b>	
<b>Product code</b>	<b>Description</b>
HV203	2 x 20w TH, NM3
HV203TD	2 x 20w TH, NM3, with time delay function
	<b>Accessories</b>
HLWG	Protective wire guard
HVBC	Battery retaining clamp