


FEATURES

- **Annealed Copper Conductor:** Provides excellent conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and mechanical stress
- **Plain Conductor Type:** Ensures smooth and efficient electrical flow
- **30/0.25 Core Strands:** Enhances flexibility and ease of installation
- **Black Jacket Colour:** Suitable for a wide range of environments and applications
- **Operating Temperature Range -15 °C to 70 °C:** Suitable for various climatic conditions
- **Voltage Rating of 500 V:** Supports high voltage applications
- **Outside Diameter of 8.6 mm:** Compact design for easy routing and installation

RS PRO 1.5 mm² Flexible Cable, 50 m

RS Stock No: 606-126



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for reliable electrical connections in various industrial and commercial settings. With a conductor size of 1.5 mm² and a length of 50 metres, it is ideal for applications requiring durable and efficient power transmission. The cable's robust construction ensures longevity and consistent performance.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	Black
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	1.5 mm ²
Cable Length	50 m
Core Strands	30/0.25
Jacket Material	Polyvinyl Chloride
Number of Cores	2
Outside Diameter	8.6 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

Electrical Specifications

Voltage	500 V
---------	-------