

LC1D50A6ED

TeSys D contactor - 3P(3 NO) - AC-3 - ≤ 440 V 50 A - 48 V DC standard coil



Main

| | |
|---|--|
| Range | TeSys |
| Product name | TeSys D |
| Product or component type | Contacteur |
| Device short name | LC1D |
| Contacteur application | Motor control Resistive load |
| Utilisation category | AC-1 AC-3 |
| Poles description | 3P |
| Pole contact composition | 3 NO |
| [Ue] rated operational voltage | ≤ 690 V AC 25...400 Hz for power circuit ≤ 300 V DC for power circuit |
| [Ie] rated operational current | 50 A (≤ 60 °C) at ≤ 440 V AC AC-3 for power circuit 80 A (≤ 60 °C) at ≤ 440 V AC AC-1 for power circuit |
| Motor power kW | 15 kW at 220...230 V AC 50/60 Hz 22 kW at 380...400 V AC 50/60 Hz 25 kW at 415 V AC 50/60 Hz 30 kW at 440 V AC 50/60 Hz 30 kW at 500 V AC 50/60 Hz 33 kW at 660...690 V AC 50/60 Hz |
| Motor power hp | 3 hp at 115 V AC 50/60 Hz for 1 phase motors 7.5 hp at 230/240 V AC 50/60 Hz for 1 phase motors 15 hp at 200/208 V AC 50/60 Hz for 3 phases motors 15 hp at 230/240 V AC 50/60 Hz for 3 phases motors 40 hp at 460/480 V AC 50/60 Hz for 3 phases motors 40 hp at 575/600 V AC 50/60 Hz for 3 phases motors |
| Control circuit type | DC standard |
| Control circuit voltage | 48 V DC |
| Auxiliary contact composition | 1 NO + 1 NC |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947 |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 80 A at ≤ 60 °C for power circuit 10 A at ≤ 60 °C for signalling circuit |
| Irms rated making capacity | 900 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 |
| Rated breaking capacity | 900 A at 440 V for power circuit conforming to IEC 60947 |
| [Icw] rated short-time withstand current | 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit 400 A ≤ 40 °C 10 s power circuit 810 A ≤ 40 °C 1 s power circuit 84 A ≤ 40 °C 10 min power circuit 208 A ≤ 40 °C 1 min power circuit |
| Associated fuse rating | 100 A gG at ≤ 690 V coordination type 1 for power circuit 100 A gG at ≤ 690 V coordination type 2 for power circuit |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

| | |
|-------------------------------|---|
| | circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1 |
| Average impedance | 1.5 mOhm at 50 Hz - lth 80 A for power circuit |
| [Ui] rated insulation voltage | 600 V for power circuit certifications CSA 600 V for power circuit certifications UL 690 V for power circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-1 600 V for signalling circuit certifications CSA 600 V for signalling circuit certifications UL |
| Electrical durability | 1.45 Mcycles 50 A AC-3 at $U_e \leq 440$ V 1.1 Mcycles 80 A AC-1 at $U_e \leq 440$ V |
| Power dissipation per pole | 3.7 W AC-3 9.6 W AC-1 |
| Protective cover | With |
| Mounting support | Plate Rail |
| Standards | EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 No 14 |
| Product certifications | BV CCC CSA DNV GL GOST RINA UL LROS |
| Connections - terminals | Control circuit : lugs-ring terminals - external diameter: 8 mm Power circuit : lugs-ring terminals - external diameter: 16.5 mm |
| Tightening torque | Control circuit : 1.7 N.m - on lugs-ring terminals - with screwdriver flat \varnothing 6 mm screw : M3.5 Control circuit : 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 screw : M3.5 Power circuit : 6 N.m - on lugs-ring terminals hexagonal 10 mm screw : M6 |
| Operating time | 16...24 ms opening 42.5...57.5 ms closing |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical durability | 10 Mcycles |
| Operating rate | 3600 cyc/h at ≤ 60 °C |

Complementary

| | |
|--------------------------------|--|
| Coil technology | Built-in bidirectional peak limiting diode suppressor |
| Control circuit voltage limits | 0.1...0.3 U_c at 60 °C drop-out 0.75...1.25 U_c at 60 °C operational |
| Time constant | 34 ms |
| Inrush power in W | 19 W at 20 °C |
| Hold-in power consumption in W | 7.4 W at 20 °C |
| Auxiliary contacts type | Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1 |
| Signalling circuit frequency | 25...400 Hz |
| Minimum switching current | 5 mA for signalling circuit |
| Minimum switching voltage | 17 V for signalling circuit |
| Non-overlap time | 1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact) |

Insulation resistance > 10 MOhm for signalling circuit

Environment

| | |
|---|--|
| IP degree of protection | IP2x front face conforming to IEC 60529 |
| Protective treatment | TH conforming to IEC 60068-2-30 |
| Pollution degree | 3 |
| Ambient air temperature for operation | -5...60 °C |
| Ambient air temperature for storage | -60...80 °C |
| Permissible ambient air temperature around the device | -40...70 °C at Uc |
| Operating altitude | 3000 m without derating in temperature |
| Fire resistance | 850 °C conforming to IEC 60695-2-1 |
| Flame retardance | V1 conforming to UL 94 |
| Mechanical robustness | Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor open 10 Gn for 11 ms Shocks contactor closed 15 Gn for 11 ms |
| Height | 122 mm |
| Width | 55 mm |
| Depth | 120 mm |
| Product weight | 0.93 kg |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Not Green Premium product |
| RoHS | Compliant - since 0001 - Schneider Electric declaration of conformity |
| Product end of life instructions | Need no specific recycling operations |