



Figure similar

SITOR fuse link, with female thread on both sides, NH2, In: 1250 A, aR, Un AC: 690 V, Un DC: 440 V, without Indicator

Model		
product brand name		SETRON
product designation		SITOR fuse link
design of the product		With female thread on both sides
design of an identification indicator		Without indicator
design of the switching contact		with female thread
design of the fuse link		Semiconductor protection fuse link
General technical data		
size of fuse system according to EN 60269-1		NH2
operating class of the fuse link		aR
varying load factor (WL)		0.85
type of voltage of the operating voltage		AC/DC
operating voltage at AC according to UL rated value		690 V
Supply voltage		
supply voltage		
• at AC		690 V
• at DC		440 V
Breaking Capacity		
switching capacity current		
• according to IEC 60947-2 rated value		100 kA
Product details		
product description		with internal thread on both sides, corrosion-free, silver-plated
accessories included		no
Mechanical Design		
mounting position		Any, preferably vertical
Environmental conditions		
ambient temperature during operation		
• minimum		-20 °C
• maximum		50 °C
environmental category		-20 to +50 at 95% relative humidity
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NC3243-6B>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NC3243-6B>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC3243-6B

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

4/11/2025 

