



Passive Components > Resistors > Surface Mount Resistors



Resistance Value: 2.2K Ω
Resistor Type: General Purpose Resistor
Element Type: Thick Film
Package Size Code: 0402
Power Rating: .063 W

Features

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thick Film
Package Size Code	0402

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	50 V
Resistance Value	2.2K Ω
Power Rating	.063 W
Resistance Class	1k Ω – 1M Ω
Passive Component Tolerance	1 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.35 mm[.014 in]
Product Length	1 mm[.039 in]
Product Width	.5 mm[.02 in]



Usage Conditions

Temperature Coefficient	±100 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1623404-1
CRG1206 1% 10K



TE Part # 1622829-1
CRG0603 1% 10K



TE Part # 1623097-1
CRG0805 1% 10K



TE Part # 1676480-1
CRG0402 1% 100K



TE Part # 1-1622826-8
[CRG0402 5% 1K0](#)

Also in the Series | [Neohm CRG](#)




[Surface Mount Resistors\(614\)](#)

Customers Also Bought



TE Part #1-1879011-3
[SMF2 680R 5%](#)



TE Part #1879666-6
[H8 150K 0.1% 15PPM](#)



TE Part #9541-010C-S-C-3-S
[PRESSURE 0.15 PSIG I2C SO16](#)



TE Part #5-1623930-2
[CFR25 5% 220K](#)




TE Part #6-1623931-6
[CFR25 5% 6K8](#)



TE Part #7-1625892-7
[3W SM M/OX 5% 18K](#)



TE Part #7-1623931-7
[CFR25 5% 820R](#)



TE Part #1-1623788-7
[SQM5 68R 5% \(WIRE\)](#)



TE Part #3-1623931-7
[CFR25 5% 47R](#)



TE Part #6-1879233-7
[SMW5 56R 5%](#)



Documents

Product Drawings

CRG0402 1% 2K2

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_4-1676480-3_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_4-1676480-3_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_4-1676480-3_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

Thick Film Chip Resistors - Type CRG series

English