




MJCC57-20-A

Ruland MJCC57-20-A, 20mm Jaw Coupling Hub, Aluminum, Clamp Style With Keyway, 57.2mm OD, 28.7mm Length



Description

Ruland MJCC57-20-A is a zero-backlash jaw coupling hub with a 20mm bore, 6mm keyway, 57.2mm OD, and 28.7mm length. It is a component in a three-piece design consisting of two aluminum hubs and an elastomeric insert called the spider creating a lightweight low inertia coupling capable of speeds up to 8,000 RPM. This three-piece design allows for a highly customizable coupling that easily combines clamp or set screw hubs with inch, metric, keyed, and keyless bores. Spiders are available in three durometers allowing the user to tailor the performance of the coupling to their application. Ruland jaw couplings have a balanced design for reduced vibration at high speeds. Hardware is metric and tests beyond DIN 912 12.9 standards for maximum torque capabilities. MJCC57-20-A is machined from bar stock that is sourced exclusively from North American mills and is RoHS2 and REACH compliant. It is manufactured in our Marlborough, MA factory under strict controls using proprietary processes.

Product Specifications

Bore B	20 mm	B1 Shaft Penetration	28.7 mm
Keyway K	6 mm	Outer Diameter OD	57.2 mm
Bore Tolerance	+0.03 mm / -.00 mm	Hub Width LH	28.7 mm
Length L	80.0 mm	Forged Clamp Screw	M6
Number of Screws	1 ea	Screw Material	Alloy Steel
Screw Finish	Black Oxide	Hex Wrench Size	5.0 mm
Seating Torque	16 Nm	Maximum Speed	8,000 RPM
Weight (lbs.)	0.4640	Temperature	-10°F to 180°F -23°C to 82°C
Material Specification	2024-T351 Aluminum Bar	Finish	Bright
Finish Specification	Bright	Manufacturer	Ruland Manufacturing
UPC	63452911632	Country of Origin	USA
Note 1	Stainless steel hubs are available upon request.		
Note 2	Performance ratings are for guidance only. The user must determine suitability for a particular application.		
Note 3	Torque ratings for the couplings are based on the physical limitations/failure point of the spiders. Under normal/typical conditions the hubs are capable of holding up to the nominal torque of the spiders. Please consult technical support for more assistance.		