

Model No. M5LFSTS

51mm wide commercial Excell® laminated steel padlock with stainless steel body cover, 38mm shackle

Best Used For:


Construction Sites & Equipment


Industrial, Storefront & Business Gates


Manufacturing Environments


Storage Buildings


Truck Doors

Overview & Features

Product Features


- Stainless steel body cover and top and bottom plates for exceptional weatherability
- 51mm wide laminated steel body for superior durability
- 38mm octagonal boron carbide shackle is 50% harder than hardened steel
- Chrome-plated shackle for excellent rust resistance
- Superior pry resistance with dual-ball bearing locking
- Can be keyed into existing K1 or WP4 Edge keyways

Product Details

The Master Lock Commercial Excell® No. M5LFSTS Laminated Steel Padlock with Stainless Steel Body Cover features a 51mm wide laminated steel body encased in a stainless steel body cover for maximum strength and weatherability. The 10mm diameter octagonal shackle is 38mm long and made of chrome-plated boron carbide, 50% harder than hardened steel, offering maximum resistance to cutting and sawing. The 4-pin cylinder prevents picking and the dual locking ball bearings provide maximum resistance against prying and hammering. Commercial Excell® offers a higher level of weatherability and security for applications in outdoor, corrosive and caustic environments.

Product Specifications

Product Number	M5LFSTS
Body Width	51mm
Shackle Dimensions	A: 10mm B: 38mm C: 24mm
Description	Keyed Different, Commercial Boxed Packaging
Shelf Pack Qty	6
Master Carton Qty	24



Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu