

Fan LXT®

DCF301

18V • ø 330 mm • 21 m³ / min

Three blowing speeds and a timer function.

This 330 mm LXT® battery or AC powered fan is an excellent companion for the summer heats. Tilts up and down and rotates left to right for convenient redirection of air flow.



Technical specifications

Max. Air Velocity	4,0 / 2,8 / 2,0 m/s
Air volume	21 / 15 / 10 m³/min
Nominal Battery Voltage	14,4 / 18 V
Product Dimensions (L x W x H):	269 x 439 x 602 mm
Tool weight with battery	4,1 - 4,5 kg
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Voltage LXT	✓
Continuous Use 18V / 5.0 Ah Battery	400 / 190 / 120 min
Continuous Use 18V / 6.0 Ah Battery	850 / 430 / 215 min
Product net weight	3,8 kg
Diameter (D)	330 mm
Angle range horizontal	180 °
Angle range vertical	135 °
Automatic rotational angle (left / right)	45 °

User benefits

- Easily removable fan cover for convenient clean-up
- Can be loaded on optional tripods
- Designed to withstand harsh job site environments
- Three speed settings (High/Medium/Low) and oscillation selector for optimal air velocity and control
- Strong enough to create a comfortable work environment under hot weather conditions
- Battery protection system automatically shuts off power when the battery level is low
- 3-stage automatic timer with 1, 2, and 4 hour power-off selection
- Powered by Makita LXT® Li-ion battery or AC adapter

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing