

KERN SXC 60K-3L

KERN

Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory



Category	
Brand	KERN
Product category	Industrial scale
Product group	Stainless steel platform scale
Product family	SXC
Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Strain gauge
Number of weighing ranges	1
Weighing capacity [Max]	60 kg
Readability [d]	0,005 kg
Reproducibility	0,005 kg
Linearity	± 0,015 kg
Resolution	12.000
Adjustment options	Adjusting with external weight
Recommended adjusting weight	60 kg (M1)
Stabilization time	3 s
Warm-up time	30 min
Eccentric loading at 1/3 [Max]	0,025 kg
Maximum creep (15 minutes)	20 g
Maximum creep (30 minutes)	40 g
Default unit	kg
Units	kg g lb ffa PCS %
Loadcell type	stainless steel IP68 encapsulated
Load cell connection	6-wire

Display

Display type	LCD
Display type	LCD with backlight
Display backlight	✓
Display screen size	160×60 mm
Display segments	6
Display digit height	48 mm
Languages of the user interface	English Symbol language

Construction

Dimension display device (W×D×H)	232×150×77,3 mm
Dimensions weighing surface (W×D)	500×400 mm
Dimensions weighing surface	500×400 mm
Dimensions weighing platform (W×D×H)	500×400×126 mm
Material weighing plate	stainless steel
Material platform	Stainless steel
Material display housing	stainless steel
Material load cell(s)	Stainless steels
Level indicator	✓
Levelling feet adjustable	✓
Stand rotatable	no
Stand inclinable	no
Wall mount	✓
Display device cable length	3 m
Allowed cable length display device [Max]	20 m
Platform Construction	Single-Cell
Load cells - number	1

Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
Percentage determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Alibi memory	optional internal memory
Alibi memory - number of memory spaces	250.000
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Counting resolution (laboratory conditions)	30.000

KERN SXC 60K-3L

KERN

Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Counting reference weight can be entered	✓	Battery / accumulator type	Li-Ion
Smallest piece weight when piece counting - laboratory conditions	2 g	Battery	no battery
Smallest piece weight when piece counting - normal conditions	20 g	Rechargeable battery operating time - backlight on	20 h
Reference quantity	5, 10, 20, 50, n (any number of pieces)	Rechargeable battery operating time - backlight off	48 h
Hold function	✓	Rechargeable battery charging time	8 h
IP protection - complete device	-	Rechargeable battery optional	Rchrg. battery optional (factory)
IP protection - display	IP68	Environmental conditions	
IP protection - platform	no IP protection	Ambient temperature [Min]	-10 °C
IP protection - load cell	IP68	Ambient temperature [Max]	40 °C
	5 min	Humidity of environment [Min]	0 %
	2 min	Humidity of environment [Max]	80 %
Auto-off interval(s) in battery mode/rechargeable battery mode	1 min 30 min 60 min 30 sec	Approval	
Auto-off interval(s) in mains power mode	off	CE mark	✓
Tare function	manual (multi)	Services (optional)	
Number of keys for operation	7	Article number for adjustment at the location of installation	961-249
Interface		Article number for DAkkS calibration	963-129
Interfaces	RS-232 (optional, factory) Ethernet (optional, factory) WiFi (optional, factory) Alibi memory (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory) Bluetooth BLE (v4.0) (optional, factory) USB-Device (optional, factory)	Article number for certificate of conformity (verification)	969-517
EasyTouch (ET) - Compatibility	vollständig	Packing & Shipping	
EasyTouch (ET) - Connection type	KUM	Delivery time	1 d
Power Supply		Dimensions packaging (W×D×H)	930×550×230 mm
Supplied power supply	Power supply unit	Net weight	20,8 kg
Plug-in power supply type	Built-in power supply	Shipping method	Parcel service
Plug-in power supply / adapter for countries - included with the delivery	EURO	Net weight approx.	22 kg
Input voltage power supply / power [Max]	110 V - 240 V AC	Gross weight approx.	26 kg
		Shipping weight	24,8 kg


KERN SXC 60K-3L

KERN

Interlinked for industry of the future: Stainless steel platform scale with up to four data interfaces and optional alibi memory

Pictograms

STANDARD



OPTION



FACTORY

