

Fiche technique

PLM4-2 Filtre de panneau Cadre galvanisé coupe-feu

Description générale

Le filtre à panneaux plissés PLM4 utilise un média classé au feu et à la toxicité selon les normes de test européennes les plus strictes.

Construction

Ce produit est construit en scellant un paquet de plis doublé en treillis soudé dans un cadre en acier galvanisé. Ce filtre utilise un média à loft profond pour assurer une longue durée de vie, une faible consommation d'énergie et un service robuste.

Caractéristiques du cadre

Acier galvanisé laminé
Coins en onglet
Bord de sécurité roulé

Les médias synthétiques

100% PET Fibres
Non-tissé thermocollé
Résistant à l'humidité



Médias FR Propriétés


DIN 53 438 \ 琺	K1/F1
NF P92-507 \ 琺	M1
NF F16-101 \ 琺	F1
CP413\ 劣	CONFORME



RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.

PLM4-2 Pleated Filters STANDARD

No.	Nominal Size Inches	Height (mm)	Width (mm)	Depth (mm)	Media Area (m ²)	Rated Airflow m ³ /hr
PLM4-2-1212	12x12x2	287	287	45	0.17	800
PLM4-2-2412	24x12x2	592	287	45	0.35	1600
PLM4-2-1515	15x15x2	368	368	45	0.28	1300
PLM4-2-1620	16x20x2	392	490	45	0.40	1900
PLM4-2-1624	16x24x2	392	592	45	0.48	2250
PLM4-2-1625	16x25x2	392	621	45	0.51	2400
PLM4-2-1818	18x18x2	445	445	45	0.41	1900
PLM4-2-2020	20x20x2	490	490	45	0.50	2340
PLM4-2-2420	24x20x2	592	490	45	0.60	2800
PLM4-2-2025	20x25x2	490	621	45	0.63	2950
PLM4-2-2424	24x24x2	592	592	45	0.73	3400
PLM4-2-610610	--	610	610	45	0.77	3600
PLM4-2-2436	24x36x2	592	892	45	1.10	5100



RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.