

## Features

- Excellent molten splash and flame resistance
- Continuous working temperature of 200°C (500°F)
- Superb abrasion and moisture resistance
- Very flexible and available in different colours
- Provides protection from ozone and UV
- Insulates against energy loss in piping and hosing
- Max short time exposure 1650°C (3000°F)
- Available in Red, Black, Yellow, Blue, White and Silver

## RS PRO Fire Sleeve White 5m

RS Stock No.: 0733522



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

RS Pro Fire Sleeve is designed to protect hoses, wires and cables from the hazards of high heat and occasional flame. Made of braided fiberglass yarns in a flexible substrate, it is then coated with high grade silicone rubber. The thick formulation of silicone rubber sheds molten splash, slag, welding splatter, electrical or grinding sparks and contamination. RS Pro Fire Sleeve's key applications are protecting hydraulic hoses, cables and wiring. Used in metallurgy, steel mills, glass works, marine industry and petrochemical industry.

## General Specifications

Part Number	Ordering Size (mm)
0731268	4
0731269	6
0731270	8
0731272	10
0731273	12
0731274	14
0731275	16
0731276	19
0731277	22
0730390	25
0730392	28
0730393	32
0730394	35
0730395	38
0733513	41
0733746	44
0733514	51
0733515	57
0733516	63
0733517	70
0733518	76
0733519	83
0733520	89
0733521	95
0733522	102
0733523	114
0733524	127
0733525	140
0733526	152
0733527	168
0733528	180
0733529	203

## Approvals

Declarations	Compiles with EN 45545-2 Tested to ISO 11925-2
Standards Met	Meets requirement for IEC 60695-11-10 Classified as HB an V0 Meets requirements for UL94 V0,V1,V2