



NO.1120020032

检 测 报 告

Test Report

样品名称： 圆柱锂离子电池 YC18650-3726-4S2P 14.8V 5200mAh
76.96Wh

Name of Sample: Cylindrical Li-ion battery YC18650-3726-4S2P 14.8V
5200mAh 76.96Wh

委托单位： 余姚煜昌电器有限公司

Consignor: /



上海化工院检测有限公司

Shanghai Research Institute of Chemical Industry Testing Co., Ltd.

声 明

Statement

1. 检测报告无本实验室公章（或检验检测专用章）无效。

The test report is invalid if it is not affixed the official seal of the laboratory to it.

2. 复制检测报告未重新加盖本实验室公章（或检验检测专用章）无效。

Copies of the test report without the official seal of the laboratory are invalid.

3. 检测报告无编制、审核、批准人签字无效。

The test report is invalid without the signatures of compiler, checker and approver.

4. 检测报告涂改无效。

The test report is invalid if it is blotted out.

5. 未经本实验室书面批准，不得部分复制检测报告。

It is forbidden to copy the test report partially without the written approval of the laboratory.

6. 送样委托检测结果，仅对所送样品有效。

The conclusion of the consignment test is only valid for the provided sample.

7. 本检测报告以中文为准，英文文本（如有）仅为译文，两者发生冲突时，应以中文文本为准。

The test report has been drafted in Chinese and translated into English (if exist) for convenience only. In the event of discrepancy, the Chinese version shall prevail.

8. 除另有说明，检测检验类别都是指委托分析。

Unless noted otherwise, the test type is consignment test.

地址：上海市云岭东路 345 号

Address: No.345 East Yunling Road, Shanghai

邮政编码(Post Code): 200062

电话(Tel): (021) 31765555

传真(Fax): (021) 31015117

网址 (web site): www.ghs.cn

电子信箱(E-mail): zmf@ghs.cn

上海化工院检测有限公司

检测报告

Shanghai Research Institute of Chemical Industry
Testing Co., Ltd. Test Report

NO. 1120020032

1/11

样品名称 Name of Sample	中文 Chinese	圆柱锂离子电池 YC18650-3726-4S2P 14.8V 5200mAh 76.96Wh			
	英文 English	Cylindrical Li-ion battery YC18650-3726-4S2P 14.8V 5200mAh 76.96Wh			
样品编号 Sample No.	1120020032				
委托单位 Consignor	余姚煜昌电器有限公司 /				
生产单位 Manufacturer	长虹格兰博科技股份有限公司 ChangHong Grand-Pro Tech Co., Ltd.				
检测方法 Test method	联合国《关于危险货物运输的建议书 试验和标准手册》 ST/SG/AC.10/11/Rev.6 Amend.1 38.3 UNITED NATIONS "Recommendations on the TRANSPORT OF DANGEROUS GOODS" Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3				
判定标准 Criterion	联合国《关于危险货物运输的建议书 试验和标准手册》 ST/SG/AC.10/11/Rev.6 Amend.1 38.3 UNITED NATIONS "Recommendations on the TRANSPORT OF DANGEROUS GOODS" Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3				
样品外观 Appearance	绿色 塑料薄膜外壳 Green Plastic film shell				
样品接受日期 Accepted Date	2020-02-17	检测起迄日期 Test Date	2020-02-25 ~ 2020-03-18		
检测项目 Test Items	高度模拟;热测试;振动;冲击;外短路;撞击;过充电;强制放电 Altitude simulation, Thermal test, Vibration, Shock, External short circuit, Impact, Overcharge, Forced discharge				
检测结论 Conclusion	经检测, 该样品符合联合国《关于危险货物运输的建议书 试验和标准手册》 ST/SG/AC.10/11/Rev.6 Amend.1 38.3标准要求。 The sample has passed the test items of UNITED NATIONS "Recommendations on the TRANSPORT OF DANGEROUS GOODS" Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 38.3 生效日期(Date): 2020-03-18				
备注 Comment	可充电锂电池组Rechargeable Lithium Battery. /				
委托单位地址 Consignor Address	/		邮政编码 Post Code 423000		

批准
Approver:
职务
Title:

张小明

副总工程师(Vice chief engineer)

审核
Checker:

陈建峰

编制
Compiler:

傅佳



上海化工院检测有限公司

检 测 报 告

Shanghai Research Institute of Chemical Industry
Testing Co., Ltd. Test Report

NO. 1120020032

2/11

序号 No.	检测项目名称 Name of Test Items	标准要求或标准条款号 Standard requirement or The Clause Number of Standard	检测结果 Test Result	本项结论 Conclusion	备注 Remark
1	高度模拟 Altitude simulation	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.1 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.1	见附表 1 See Appendix 1	合格 Passed	/
2	热测试 Thermal test	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.2 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.2	见附表 2 See Appendix 2	合格 Passed	/
3	振动 Vibration	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.3 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.3	见附表 3 See Appendix 3	合格 Passed	/
4	冲击 Shock	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.4 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.4	见附表 4 See Appendix 4	合格 Passed	/
5	外短路 External short circuit	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.5 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.5	见附表 5 See Appendix 5	合格 Passed	/
6	撞击 Impact	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.6 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.6	见附表 6 See Appendix 6	合格 Passed	/
7	过充电 Overcharge	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.7 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.7	见附表 7 See Appendix 7	合格 Passed	/
8	强制放电 Forced discharge	联合国《关于危险货物运输的建议书 试验和标准手册》ST/SG/AC.10/11/Rev.6 Amend.1 38.3 试验T.8 UN Manual of Tests and Criteria ST/SG/AC.10/11/Rev.6 Amend.1 Section 38.3 Test T.8	见附表 8 See Appendix 8	合格 Passed	/
检测环境条件 Test Environment Condition		环境温度:21℃-23℃;环境湿度:/% Ambient temperature:21℃-23℃;Ambient humidity:/%			
分包检验情况 Subcontracted Test Condition		检测项目 Test Item	/		
		分包实验室 Subcontracted Laboratory	名称 Name	/	邮编 Post Code
			地址 Address	/	电话 Tel

SRICI Testing Co., Ltd. Test Report—Appendix 1 NO. 1120020032

[illegible]

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

SRICI Testing Co., Ltd. Test Report—Appendix 2

4/11

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

5/11

备注: L-泄漏 V-漏气 D-解体 R-破裂 F-起火 O-无泄漏、无漏气、无解体、无破裂、无起火。
Note: L-Leakage V-Venting D-Disassembly R-Rupture F-Fire O-No Leakage, No Venting,
No Disassembly, No Rupture & No Fire.

SRICI Testing Co., Ltd. Test Report—Appendix 4 NO. 1120020032

[illegible]

序号 No.	5	检测项目名称 Name of Test Items	外短路 External short circuit
样品编号 Sample No.	样品状态 Sample Status	样品表面最高温度 Max. External Temperature /℃	其他现象 Other Event
001	1CYC完全充电 1CYC Fully charged	57.2	O
002	1CYC完全充电 1CYC Fully charged	57.9	O
003	1CYC完全充电 1CYC Fully charged	58.1	O
004	1CYC完全充电 1CYC Fully charged	58.6	O
005	25CYC完全充电 25CYC Fully charged	58.9	O
006	25CYC完全充电 25CYC Fully charged	56.7	O
007	25CYC完全充电 25CYC Fully charged	56.7	O
008	25CYC完全充电 25CYC Fully charged	56.9	O
以下空白	This space intentionally left blank		

备注：D-解体 R-破裂 F-起火 O-无解体、无起火、无破裂。
Note: D-Disassembly R-Ruptur F-Fire O-No Disassembly,No Fire & No Rupture.

SRICI Testing Co., Ltd. Test Report—Appendix 6

8/11

备注: D-解体 F-起火 0-无解体、无起火。

Note: D-Disassembly F-Fire O-No Disassembly & No Fire.

SRICI Testing Co., Ltd. Test Report—Appendix 7 NO. 1120020032

NO. 1120020032

备注: D-解体 F-起火 O-无解体、无起火。
Note: D-Disassembly F-Fire O-No Disassembly & No Fire.

上海化工院检测有限公司
检测报告-附表 8

SRICI Testing Co., Ltd. Test Report—Appendix 8 NO. 1120020032

10/11

10/11

序号 No.	8	检测项目名称 Name of Test Items	强制放电 Forced discharge
样品编号 Sample No.	样品状态 Sample Status	其他现象 Other Event	
027	1CYC完全放电 1CYC Fully discharged	O	
028	1CYC完全放电 1CYC Fully discharged	O	
029	1CYC完全放电 1CYC Fully discharged	O	
030	1CYC完全放电 1CYC Fully discharged	O	
031	1CYC完全放电 1CYC Fully discharged	O	
032	1CYC完全放电 1CYC Fully discharged	O	
033	1CYC完全放电 1CYC Fully discharged	O	
034	1CYC完全放电 1CYC Fully discharged	O	
035	1CYC完全放电 1CYC Fully discharged	O	
036	1CYC完全放电 1CYC Fully discharged	O	
037	25CYC完全放电 25CYC Fully discharged	O	
038	25CYC完全放电 25CYC Fully discharged	O	
039	25CYC完全放电 25CYC Fully discharged	O	
040	25CYC完全放电 25CYC Fully discharged	O	
041	25CYC完全放电 25CYC Fully discharged	O	
042	25CYC完全放电 25CYC Fully discharged	O	
043	25CYC完全放电 25CYC Fully discharged	O	
044	25CYC完全放电 25CYC Fully discharged	O	
045	25CYC完全放电 25CYC Fully discharged	O	
046	25CYC完全放电 25CYC Fully discharged	O	
备注: D-解体 F-起火 O-无解体、无起火。 Note: D-Disassembly F-Fire O-No Disassembly & No Fire.			

上海化工院检测有限公司
检测报告-附图

SRICI Testing Co., Ltd. Test Report—Appendix NO. 1120020032

11/11



报告结束