

XID150

Features:

- Pressure developing, centrifugal fans suitable for extract or intake.
- Comprehensive 6 model range.
- Compact and robust zintec steel construction.
- Can be mounted to run in any position.
- Designed for ease of installation and low maintenance.
- Totally enclosed, lubricated for life motors.
- Motors protected to IP44.
- Speed controller available for all models.
- Standard thermal overheat protection.
- 3 year guarantee (UK - ONLY).
- Export Customers see your Local Distributor.




Performance:

Standard models are single phase 240V 50Hz. The electrical connection terminal box, protected to IP54, also contains the motor capacitor. A 20mm diameter entry and grommet is provided. All models can be operated direct by a remote switch (not provided) or a speed controller model XIC1 available as an ancillary.

Air Flow at FID (m ³ /sec):	0.175
Sound Pressure (dB(A)):	54
RPM:	2600
Weight (kg):	3.7
Max Ambient Temperature:	40
Frequency (Hz):	50
Ducting Dia. (mm):	150 (5.91 inches)
Voltage:	240V
Mounting:	Ducted
Usage:	Pub, Bar, Cafe, Restaurant, Public Toilet

XID150

Performance



XID RANGE