




Introducing the **Easy Series**

Essential automation & control products

When just enough is just right!



Easy Harmony XB2 metal

Control and signaling units Ø 22



Harmony

Discover [Harmony](#)

Advanced operator interface and industrial relays

Harmony operator interface and industrial relays enhance operational efficiency and equipment availability across industrial and building applications. **Harmony** includes intelligent connected products and edge terminals that visualize, gather and process data, enabling informed operator decisions

Explore our offer

- [Harmony](#) Push Buttons and Switches
- [Harmony](#) HMI Operator Terminals, IPC and EdgeBox
- [Harmony](#) Signaling Devices
- [Harmony](#) Electrical Relays
- [Harmony](#) Safety

Life Is On

Schneider
Electric

Quick access to product information

Get technical information about your product


References

Modicon TM3
I/O expansion modules for Modicon controllers
Analog I/O modules


References	Input range	Output range	Resolution	Input terminal block (T)	Reference	Weight
2 voltage/current inputs	-15...+15 VDC 0...+10 VDC 0...20 mA A, 20 mA	15 000 mV 10 000 mV 10 000 mV	16 bits 16 bits 16 bits	0 580 0 2 0 580 0 2 0 580 0 2	TM3AI2H TM3AI2H TM3AI2H	0.150 0.150 0.150
4 voltage/current inputs	-15...+15 VDC 0...+10 VDC 0...20 mA A, 20 mA	15 000 mV 10 000 mV 10 000 mV	16 bits 16 bits 16 bits	0 580 0 2 0 580 0 2 0 580 0 2	TM3AI4H TM3AI4H TM3AI4H	0.200 0.200 0.200
4 voltage/current or temperature inputs (T)	Thermocouples (T) J, K, R, S, E, T, N, B, C Temperature inputs (I) PT100, PT500, PT1000 0...+10 VDC 0...20 mA A, 20 mA	15 000 mV 10 000 mV 10 000 mV	16 bits 16 bits 16 bits	0 580 0 2 0 580 0 2 0 580 0 2	TM3AI4T TM3AI4T TM3AI4T	0.200 0.200 0.200
4 differential temperature inputs	Thermocouples (T) J, K, R, S, E, T, N, B, C Temperature inputs (I) PT100, PT500, PT1000 0...+10 VDC 0...20 mA A, 20 mA	15 000 mV 10 000 mV 10 000 mV	16 bits 16 bits 16 bits	0 580 0 2 0 580 0 2 0 580 0 2	TM3AI4T TM3AI4T TM3AI4T	0.200 0.200 0.200
4 voltage/current inputs	-15...+15 VDC 0...+10 VDC 0...20 mA A, 20 mA	15 000 mV 10 000 mV 10 000 mV	16 bits 16 bits 16 bits	0 580 0 2 0 580 0 2 0 580 0 2	TM3AI4H TM3AI4H TM3AI4H	0.200 0.200 0.200

Each commercial reference presented in a catalog contains a hyperlink. Click on it to obtain the technical information of the product:


- Characteristics, Dimensions and drawings, Mounting and clearance, Connections and schemas, Performance curves
- Product image, Instruction sheet, User guide, Product certifications, End of life manual



Find your catalog



- > With just 3 clicks, you can access the Industrial Automation and Control catalogs, in both English and French
- > Consult digital automation catalogs at [Digi-Cat Online](#)




- Up-to-date catalogs
- Embedded product selectors, 360° pictures
- Optimized search by commercial references

Select your training



- > Find the right [Training](#) for your needs on our Global website
- > Locate the training center with the selector tool, using this [link](#)



Life Is On

Schneider
Electric

General contents

Easy Harmony XB2

■ General presentation	page 2
<i>Selection guide</i>	page 4
■ General	
□ Presentation	page 10
□ Description	page 12
■ References	
□ Spring return pushbuttons, flush or projecting	page 16
□ Spring return pushbuttons, booted or mushroom	page 17
□ Selector switches, standard, long handle or key	page 18
□ Illuminated pushbuttons with flush push	page 19
□ Joystick controllers	page 19
□ Annunciators	page 19
□ Pushbutton sub-assemblies	page 20
□ Emergency and illuminated pushbutton sub-assemblies	page 22
□ Selector switches sub-assemblies	page 23
□ Light blocks	page 24
□ Pilot lights with integral LED	page 25
□ Contact functions and bulbs	page 27
□ Accessories	page 28
□ Empty plastic control stations	page 30
■ Product reference index.....	page 32

Easy Harmony XB2:

- modular, metal pushbuttons and switches
- complete, plastic pilot lights with integral LED

Fit for purpose

The Easy Harmony XB2 range products are designed to be used in numerous control and signaling applications:

- > customer can easily select the key functions for standard applications
- > the diameter of pushbutton head is Ø 22 mm / 0.866 in. which makes them suitable for standard OEM and panel builder applications
- > with metal bezels and mountings, they provide a solution for industrial applications demanding a high resistance to vibration and shock

Ease and comfort of choice

The range is available in the form of complete units and sub-assemblies. It involves:

- > modular, metal pushbuttons and switches with metal bezels and fixing collar. The modular design allows flexible and simple setup for complete products: the right product can be chosen among various types of heads and 2 types of functions are proposed (contact and signaling)
- > complete pilot lights, provided with integral LED

All products are fitted with screw clamp terminals allowing fast and easy connection.

Contact functions

- Pushbuttons (marked or unmarked) with spring return and push-push module option
- Selector switches and key switches, 2 or 3 positions.
- Emergency switching off and emergency stop pushbuttons with push-pull and turn to release
- 2 and 4 way joysticks with spring return or stay put



Contact and signaling functions

- Illuminated pushbuttons with integral LED, spring return and flush push




Signaling functions

- Pilot lights with integral LED
- Illuminated or non-illuminated annunciators



Groomed ergonomics


- > Metal bezel on push buttons and switches provide robustness
- > Ergonomic curve on the selector switches allows flexible operation




Easy installation

- > Installation of pushbuttons is quick and easy
- > Mounting by dual screw to the control panel ensures
 - Anti-rotation
 - Grounding contact to panel

- Push in and turn head installation for head
- Tighten head to fixing base via screws attached



- Screw together system for contact blocks and push-push module



Proven robustness

- > Conforming to most demanding international standards and approvals
- > Tested and certified performance
- > Excellent resistance to mechanical shock and vibration
- > Support an extended operating storage temperature range from -25°C to 70°C



Helps customers to
improve reliability

Service and availability

- > Supported by the service of Schneider Electric
- > Wide availability throughout an extensive distribution network

Control and signaling units Ø 22
Easy Harmony XB2 metal
Pushbuttons, switches, and pilot lights

Type of products		Contact functions		
		Pushbuttons	Emergency switching off pushbuttons	Emergency stop pushbuttons
		 	 	
Description of range		■ Pushbuttons, spring return: flush push, projecting push, booted push, mushroom push ■ Emergency switching off pushbutton: turn to release and push-pull ■ Emergency stop pushbutton: push-pull and turn to release		
Features	Products	Complete units		
	Shape of head	Circular		
Drilling or cut-out for mounting		Ø 22 mm/0.866 in.		
Degree of protection		IP65, IP66	IP65	
International standards		EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-4, GB/T 14048.5, GB/T 14048.1		EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-5, GB/T 14048.1, GB/T 14048.5, GB/T 14048.14
Product certification		CCC, CE		
Cabling		Screw clamp terminal connections		
Mounting	Panel thickness	1 to 6 mm/ 0.04 to 0.24 in.		
Type references		XB2BA●●C/ XB2BL●●C/ XB2BP●●C/ XB2BC●●C	XB2BT42EC/ XB2BS●42C	XB2BT842C/ XB2BS8442C
Pages		16 and 17	17	17

Contact functions	Contact and signaling functions	
	Selector and key switches	Illuminated pushbuttons
	 	 
■ Selector switches, 2 or 3-position: standard or long handle ■ Key selector switches		■ Illuminated pushbuttons with LED, spring return: flush push
Complete units		
Circular		
Ø 22 mm/0.866 in.		
IP65		
EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-4, GB/T 14048.5, GB/T 14048.1		
CCC, CE		
Screw clamp terminal connections		
1 to 6 mm/0.04 to 0.24 in.		
XB2BD●●C/ XB2BJ●●C/ XB2BG●●C		XB2BW●●B1C/ XB2BW●●M1C
18		19

Control and signaling units Ø 22
Easy Harmony XB2 metal
Pushbuttons, switches, and pilot lights

Type of products	Heads only		
	Pushbutton heads	Emergency switching off heads	Emergency stop heads
	 	  	
Description of range	■ Pushbuttons, spring return heads: flush push, projecting push, booted push, mushroom push		
Features	Head only		
	Circular		
Drilling or cut-out for mounting	Ø 22 mm/0.866 in.		
Degree of protection	IP65 (Front), IP66		IP65
	EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-4, GB/T 14048.5, GB/T 14048.1		EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-5, GB/T 14048.1, GB/T 14048.5, GB/T 14048.14
Product certification	CCC, CE		
Mounting	Panel thickness Ø 1 to 6 mm/0.04 to 0.24 in.		
Type references	ZB2BA●C/ ZB2BL●C/ ZB2BP●C/ ZB2BC●C	ZB2BT4EC/ ZB2BS●●C	ZB2BT84C/ ZB2BS844C
Pages	20 and 21	22	22

Heads only	
Selector switch heads	Illuminated pushbutton heads
 	
■ Selector switches, 2 or 3-position heads: standard or long handle ■ Key switches	
Head only	
Circular	
Ø 22 mm/0.866 in.	
IP65 (Front)	
EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-4, GB/T 14048.5, GB/T 14048.1	
CCC, CE	
Ø 1 to 6 mm/0.04 to 0.24 in.	
ZB2BD●C/ ZB2BJ●C/ ZB2BG●C	ZB2BW●●C
23	22

Control and signaling units Ø 22
Easy Harmony XB2 metal
Pushbuttons, switches, and pilot lights

Type of products		Contact function		
		Light bodies	Contact functions	Joystick controllers
				
Description of range		■ Light bodies with collars	■ Contact functions	■ Joystick controllers
Features	Products	Sub assembly		Complete units
	Shape of head	–		Circular
Drilling or cut-out for mounting		Ø 22 mm/0.866 in.		
Degree of protection		IP20		IP65
International standards		EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-4, GB/T 14048.5, GB/T 14048.1		
Product certification		CCC, CE		
Cabling		Screw clamp terminal connections		
Mounting	Panel thickness	1 to 6 mm/0.04 to 0.24 in.		
Type references		ZB2BW06●C/ ZB2BWB●●C/ ZB2BWM●●C	ZB2BZ10●C / ZB2BE10●C	XD2PA●●CR
Pages		24	27	19

Signaling function		
Annunciators	Pilot lights	Other accessories
		
■ Annunciators	■ Pilot lights with integral LED	■ Other accessories
Complete units		–
Circular		–
Ø 22 mm/0.866 in.		–
IP40	IP65 conforming to standard IEC 60529	–
EN/IEC 60947-1, EN/IEC 60947-5-1, EN/IEC 60947-5-4, GB/T 14048.5, GB/T 14048.1		–
CCC, CE		–
Screw clamp terminal connections		–
1 to 6 mm/0.04 to 0.24 in.		–
XB2BS●C/ XB2BS●4LC	XA2EV●●LC/EV●E●LC/ EV●D●LC/EV●●34LC	ZB2BY●●●●C/ ZB2BZ●●C/ ZB2BZ●●●●C/ ZBP●C / DL1-LED24● / DL1-LED110● / DL1-LED220●
19	25	27 and 28

Control and signaling units Ø 22

Easy Harmony XB2, metal

Pushbuttons, switches, and pilot lights



Presentation

The Easy Harmony XB2 metal range of modular control and signaling units combines simplicity of installation, flexibility, and robustness. It meets the requirements of the majority of basic industrial applications. These units are available as complete products or separate components for customer assembly.

■ This range includes:

- Pushbuttons, selector/key switches, Emergency stop/switch off functions, designed for parameter settings, adjustments, and start/stop control of machines and installations
- Special functions such as joysticks for jog, control adjustments
- Illuminated pushbuttons, pilot lights and buzzer functions are designed for visual or audio signaling
- Various accessories including push-pull module, protective dust cap, legends and legend holders are available for this range



■ The pushbutton and switch control offer (illuminated and non-illuminated) is both broad and comprehensive:


- Pushbuttons, spring return with flush push, projecting push, booted flush push, or mushroom head
- Emergency stop and switch off pushbuttons with 2 types of head: push-pull and turn to release
- Illuminated pushbuttons with integral LED and BA 9s base fitting bulbs
- Selector switches with different types of operator: standard handle, long handle, or key
- Colors of push: white, black, green, blue, red, or yellow
- Connection type: screw clamp connector
- Contact blocks for general purpose
- Choice of heads to meet the majority of basic industrial needs: pushbuttons and pilot from the most basic pushbuttons and pilot lights.
- Wide choice of accessories
- Other specific functions: complete joystick controllers and buzzers.

Easy Harmony XB2 range of control and signaling units
for Ø 22 mm/0.866 in. mounting

Installation

- Easy Harmony XB2 products are both simple and quick to install:
 - Insert the head and turn into the body component system
 - Mounting by double screw (self-maintaining head in its cut-out)
 - Anti-loosening system for screw clamp terminals on contact blocks

Easy Harmony XB2 standard mounting products are installed without a notch in a Ø 22 mm/0.866 in. hole.



For installation of Easy Harmony XB2 standard mounting products

Environment

- Certified and approved for meeting requirements throughout all continents: EN/IEC, CEC, CCC
- Protection against ingress of solid objects, dust, and water: IP65, IP66 (boot PB), IP40 (buzzer)
- International standards: IEC 60947-5-1, IEC 60947-5-5, EN 60947-5-1, EN 60947-5-5, GB/T 14048.1, GB/T 14048.5, GB/T 14048.14
- Operating temperature range from -25°C to +70°C/ -13°F to +158°F for outdoor applications
- High vibration resistance with shock proof connection screws (periodic retightening unnecessary)

Control and signaling units Ø 22

Easy Harmony XB2, metal

Pushbuttons, switches, and pilot lights: complete units

Complete units

Contact functions

Pushbuttons, spring return	Type of push	Flush push, unmarked		Flush push, marked		Projecting push, unmarked	
	Degree of protection	IP65		IP65		IP65	
	Color	White, Black, Green, Red, Yellow, and Blue		White, Black, Green, Red, and Blue		Black, Green, and Red	
	Reference	XB2BA●●C		XB2BA●●●●C		XB2BL●●C	
	Pages	16		16		16	
							
Pushbuttons, spring return	Type of push	Booted push, unmarked		Mushroom push, unmarked			
	Degree of protection	IP66		IP65			
	Color	Black, Green, and Red		Black, Green, Red and Yellow			
	Reference	XB2BP●●C		XB2BC●●C			
	Pages	17		17			
				 			
Emergency stop and switching off pushbuttons	Type of push	Trigger turn to release and push-pull (Ø 40 mm/1.575 in.)		Turn to release (Ø 30 mm/1.181 in., Ø 40 mm/1.575 in., Ø 60 mm/1.362 in.) and push-pull (Ø 40 mm/1.575 in.)			
	Degree of protection	IP65		IP65			
	Color	Red		Red			
	Reference	XB2BS8442C/ XB2BT842C		XB2BS●42C/ XB2BT42EC			
	Pages	17		17			
							
Selector switches and key switches	Type of push	Standard handle, 2 or 3 positions		Long handle, 2 or 3 positions		Key, 2 or 3 positions	
	Degree of protection	IP65		IP65		IP65	
	Color	Black		Black		Black	
	Reference	XB2BD●●C		XB2BJ●●C		XB2BG●●C	
	Pages	18		18		18	

Complete units (continued)

Illuminated pushbuttons, spring return	Type of push
	Degree of protection
	Incoming voltage
	Color
	Reference
	Pages

Contact functions



Flush push
IP65
BA 9S Integral LEDs 24, 220...230 V
White, Green, Red, Orange, and Blue
XB2BW3●B1C/XB2BW3●M1C
19

Joystick, stay put or spring return	Type of push
	Degree of protection
	Reference
	Pages



Standard handle, 2 or 4 positions
IP65
XD2PA●●CR
19

Buzzers, illuminated and non-illuminated	Degree of protection
	LED
	Color
	Reference
	Pages



IP40
Integral LEDs 24 or 220...230 V
Red and Black
XB2BS●C/ XB2BS●4LC
19

Complete units (continued)

Signaling functions



Pilot lights	Degree of protection
	LED
	Color
	Reference
	Pages

IP65
Integral LEDs 12 V, 24 V, 30 V, 48 V, 60...63.5 V, 110 V, 220...230 V, and 380...400 V
White, Green, Red, Orange, Blue, Yellow and Bi-color (Green/Red)
XA2EV●●LC/EV●E●LC/EV●D●LC/EV●●34LC
25

Sub assembly units		Head functions		
Pushbutton head, spring return	Type of push			
	Degree of protection	IP65	IP65	IP65
	Color	White, Black, Green, Red, Yellow and Blue	White, Black, Green, Red and Blue	Black, Green, Red and Yellow
	Reference	ZB2BA●C	ZB2BA●●●C	ZB2BL●C
	Pages	20	20	20
Pushbutton head, spring return	Type of push			
	Degree of protection	IP66	IP65	IP65
	Color	Black, Green, Red, Yellow and Blue	Black, Green, Red, Yellow and Blue	White, Green, Red, Orange and Blue
	Reference	ZB2BP●C	ZB2BC●C/ ZB2BR●C	ZB2BW●●C
	Pages	21	21	22
Emergency stop and switching off pushbuttons	Type of push			
	Degree of protection	IP65	IP65	
	Color	Red	Red and Black	
	Reference	ZB2BS844C/ ZB2BT84C	ZB2BT4EC/ ZB2BS●4C	
	Pages	22	22	
Selector switches and key switches head	Type of push			
	Degree of protection	IP65	IP65	IP65
	Color	Black	Black	Black
	Reference	ZB2BD●C	ZB2BJ●C	ZB2BG●C
	Pages	23	23	23

Sub assembly units (continued)

Contact functions



Light blocks, spring return	Type of contact block	Normally open/ normally closed with fixing collar	Fixing collar with light block and contact blocks
	LED	—	BA 9S Integral LEDs 24, 220...230 V
	Color	—	—
	Reference	ZB2BZ10●C	ZB2BWB●●C/ZB2BWM●●C/ZB2BW06●C
	Pages	24	24



	Type of function	Normally open/ normally closed
	Color	—
	Reference	ZB2BE10●C
	Pages	27





Push push module	Type of push	Push push module
	Degree of protection	—
	Color	Black
	Reference	ZB2BZ21C
	Pages	27

Control and signaling units Ø 22

Easy Harmony XB2 metal

Spring return pushbuttons, flush or projecting



Spring return pushbuttons with flush push

Shape of head	Type of contacts		Color of push	Marking	Reference	Weight kg/lb
	NO	NC				
Unmarked						
	1	—	White	Unmarked	XB2BA11C (ZB2BZ101C + ZB2BA1C)	0.070/0.154
	1	—	Black	Unmarked	XB2BA21C (ZB2BZ101C + ZB2BA2C)	0.070/0.154
	1	—	Green	Unmarked	XB2BA31C (ZB2BZ101C + ZB2BA3C)	0.070/0.154
	1	—	Yellow	Unmarked	XB2BA51C (ZB2BZ101C + ZB2BA5C)	0.070/0.154
	1	—	Blue	Unmarked	XB2BA61C (ZB2BZ101C + ZB2BA6C)	0.070/0.154
	—	1	Red	Unmarked	XB2BA42C (ZB2BZ102C + ZB2BA4C)	0.070/0.154
Marked						
	1	—	Green	"I"	XB2BA3311C (ZB2BZ101C + ZB2BA331C)	0.070/0.154
	1	—	Black	↓	XB2BA3351C (ZB2BZ101C + ZB2BA335C)	0.070/0.154
	1	—	White	↑	XB2BA3341C (ZB2BZ101C + ZB2BA334C)	0.070/0.154
	—	1	Red	"O"	XB2BA4322C (ZB2BZ102C + ZB2BA432C)	0.070/0.154

Spring return pushbuttons with projecting push

Shape of head	Type of contacts		Color of push	Marking	Reference	Weight kg/lb
	NO	NC				
Unmarked						
	1	—	Green	Unmarked	XB2BL31C (ZB2BZ101C + ZB2BL3C)	0.070/0.154
	—	1	Red	Unmarked	XB2BL42C (ZB2BZ102C + ZB2BL4C)	0.070/0.154



XB2BP21C

Booted pushbuttons, spring return						
Shape of head		Type of contacts		Color of push	Reference	Weight kg/lb
		NO	NC			
		1	–	Black	XB2BP21C (ZB2BZ101C+ZB2BP2C)	0.070/0.154
		1	–	Green	XB2BP31C (ZB2BZ101C+ZB2BP3C)	0.070/0.154
		–	1	Red	XB2BP42C (ZB2BZ102C+ZB2BP4C)	0.070/0.154



XB2BC51C

Mushroom head pushbuttons, spring return						
Shape of head		Type of contacts		Color of push	Diameter Ø (mm)/in.	Reference
		NO	NC			
		1	–	Black	40/1.575	XB2BC21C (ZB2BZ101C+ZB2BC2C)
		1	–	Green	40/1.575	XB2BC31C (ZB2BZ101C+ZB2BC3C)
		1	–	Yellow	40/1.575	XB2BC51C (ZB2BZ101C+ZB2BC5C)
		–	1	Red	40/1.575	XB2BC42C (ZB2BZ102C+ZB2BC4C)
		1	–	Black	60/2.362	XB2BR21C (ZB2BZ101C+ZB2BR2C)



XB2BR21C

Emergency switching off pushbuttons						
Shape of head	Type of push	Type of contacts		Color of push	Diameter Ø (mm)/in.	Reference
		NO	NC			
	Push-pull	–	1	Red	40/1.575	XB2BT42EC (ZB2BZ102C+ZB2BT4EC)
	Turn to release	–	1	Red	30/1.181	XB2BS442C (ZB2BZ102C+ZB2BS44C)
				Red	40/1.575	XB2BS542C (ZB2BZ102C+ZB2BS54C)
				Red	60/2.362	XB2BS642C (ZB2BZ102C+ZB2BS64C)



XB2BT42EC

Emergency stop pushbuttons (1)						
Shape of head	Type of push	Type of contacts		Color of push	Diameter Ø (mm)/in.	Reference
		NO	NC			
	Push-pull	–	1	Red	40/1.575	XB2BT842C (ZB2BZ102C+ZB2BT84C)
	Turn to release	–	1	Red	40/1.575	XB2BS8442C (ZB2BZ102C+ZB2BS844C)



XB2BS8442C

(1) Emergency stop pushbuttons should have a maximum of 4 contact blocks, installed in 2 rows only.

Control and signaling units Ø 22

Easy Harmony XB2 metal

Selector switches, standard, long handle or key

XB2B-XA2B_CP22085



XB2BJ21C

Selector switches, with standard handle or with long handle							
Shape of head	Type of push	Type of contacts		Positions		Reference	Weight
				Number	Type		
	Standard handle, black	1	—	2 - stay put		XB2BD21C (ZB2BZ101C + ZB2BD2C)	0.096/0.212
		1	1			XB2BD25C (ZB2BZ105C + ZB2BD2C)	0.096/0.212
		1	—	2- spring return		XB2BD41C (ZB2BZ101C + ZB2BD4C)	0.085/0.187
		1	1			XB2BD45C (ZB2BZ105C + ZB2BD4C)	0.100/0.220
		2	—	3-stay put		XB2BD33C (ZB2BZ103C + ZB2BD3C)	0.100/0.220
		2	—	3- spring return from 2 sides		XB2BD53C (ZB2BZ103C + ZB2BD5C)	0.100/0.220
	Long handle	2	—	3- spring return from 1 side		XB2BD73C (ZB2BZ103C + ZB2BD7C)	0.100/0.220
		1	—	2 - stay put		XB2BJ21C (ZB2BZ101C + ZB2BJ2C)	0.085/0.187
		1	1			XB2BJ25C (ZB2BZ105C + ZB2BJ2C)	0.100/0.220
		2	—	3 - stay put		XB2BJ33C (ZB2BZ103C + ZB2BJ3C)	0.100/0.220
		2	—	3- spring return from 2 sides		XB2BJ53C (ZB2BZ103C + ZB2BJ5C)	0.100/0.220

Key selector switches

Shape of head	Type of push	Type of contacts		Positions		Reference	Weight
		NO	NC	Number	Type		
	Key	1	–	2 - stay put, 1 side pull out		XB2BG21C (ZB2BZ101C + ZB2BG2C)	0.110/0.242
		1	1			XB2BG25C (ZB2BZ105C + ZB2BG2C)	0.125/0.275
		1	–	2 - stay put, 2 side pull out		XB2BG41C (ZB2BZ101C + ZB2BG4C)	0.078/0.171
		1	1			XB2BG45C (ZB2BZ105C + ZB2BG4C)	0.078/0.171
		1	–	2 - spring return, 1 side pull out		XB2BG61C (ZB2BZ101C + ZB2BG6C)	0.110/0.242
		1	1			XB2BG65C (ZB2BZ105C + ZB2BG6C)	0.125/0.275
		2	–	3 - stay put, middle pull out		XB2BG33C (ZB2BZ103C + ZB2BG3C)	0.125/0.275
		2	–	3 - stay put, 2 sides pull out		XB2BG53C (ZB2BZ103C + ZB2BG5C)	0.125/0.275
		2	–	3 - stay put, 3 sides pull out		XB2BG03C (ZB2BZ103C + ZB2BG0C)	0.125/0.275

XB2B-XA2B_CP22071



XB2BG21C



XB2BW31B1C

Illuminated pushbuttons with integral LED							
Shape of head	Type of push	Supply voltage V	Type of contacts		Color	Reference	Weight kg/lb
			NO	NC			
	Flush push	24 ~	1	—	White	XB2BW31B1C (ZB2BWB11C + ZB2BW31C)	0.120/0.264
					Green	XB2BW33B1C (ZB2BWB31C + ZB2BW33C)	0.120/0.264
					Red	XB2BW34B1C (ZB2BWB41C + ZB2BW34C)	0.120/0.264
					Orange	XB2BW35B1C (ZB2BWB51C + ZB2BW35C)	0.120/0.264
					Blue	XB2BW36B1C (ZB2BWB61C + ZB2BW36C)	0.120/0.264
		220-230 ~	1	—	White	XB2BW31M1C (ZB2BWM11C + ZB2BW31C)	0.120/0.264
					Green	XB2BW33M1C (ZB2BWM31C + ZB2BW33C)	0.120/0.264
					Red	XB2BW34M1C (ZB2BWM41C + ZB2BW34C)	0.120/0.264
					Orange	XB2BW35M1C (ZB2BWM51C + ZB2BW35C)	0.120/0.264
					Blue	XB2BW36M1C (ZB2BWM61C + ZB2BW36C)	0.120/0.264



XD2PA12CR

Joystick controllers				
Description	Operation position	Spring return	Reference	Weight kg/lb
Complete products				
2-direction	1 notch	Without	XD2PA12CR	0.115/0.253
	1 NO per direction	With	XD2PA22CR	0.115/0.253
4-direction	1 notch	Without	XD2PA14CR	0.145/0.319
	1 NO per direction	With	XD2PA24CR	0.145/0.319



XB2BSB4LC

Annunciators				
Description	Supply voltage V	Color	Reference	Weight kg/lb
Non-illuminated 90dB	24 ~ - 50/60 Hz	Black	XB2BSBC	0.017/0.037
	220...230 ~ - 50/60 Hz		XB2BSMC	0.017/0.037
Illuminated 90dB	24 V ~ - 50/60 Hz	Red	XB2BSB4LC	0.020/0.044
	220...230 V ~ - 50/60 Hz		XB2BSM4LC	0.020/0.044

Control and signaling units Ø 22

Easy Harmony XB2 metal

Pushbutton sub-assemblies

XB2B-XA2B_CP22012



ZB2BA5C

Pushbuttons with flush push					
Shape of head	Type of push	Marking	Color of push	Reference	Weight kg/lb
Heads only					
	Spring return	Unmarked	White	ZB2BA1C	0.030/0.066
			Black	ZB2BA2C	0.030/0.066
			Green	ZB2BA3C	0.030/0.066
			Red	ZB2BA4C	0.030/0.066
			Yellow	ZB2BA5C	0.030/0.066
			Blue	ZB2BA6C	0.030/0.066

XB2B-XA2B_CP22038



ZB2BA651C

	Spring return		Green	ZB2BA331C	0.030/0.066
			Black	ZB2BA335C	0.030/0.066
			White	ZB2BA334C	0.030/0.066
			Blue	ZB2BA651C	0.030/0.066
			Red	ZB2BA432C	0.030/0.066
			Red	ZB2BA434C	0.030/0.066

Pushbuttons with projecting push					
Shape of head	Type of push	Marking	Color of push	Reference	Weight kg/lb
Heads only					
	Spring return	Unmarked	Black	ZB2BL2C	0.030/0.066
			Green	ZB2BL3C	0.030/0.066
			Red	ZB2BL4C	0.030/0.066
			Yellow	ZB2BL5C	0.030/0.066
	Spring return	"O"	Red	ZB2BL432C	0.030/0.066

XB2B-XA2B_CP22019



ZB2BL3C

XB2B-XA2B_CP22039



ZB2BL432C

XB2B-XA2B_CP22028



ZB2BP3C

Booted pushbutton heads with spring return				
Shape of head	Type of push	Color of push	Reference	Weight kg/lb
Heads only				
	Spring return	Black	ZB2BP2C	0.025/0.055
		Green	ZB2BP3C	0.025/0.055
		Red	ZB2BP4C	0.025/0.055
		Yellow	ZB2BP5C	0.025/0.055
		Blue	ZB2BP6C	0.025/0.055

XB2B-XA2B_CP22044



ZB2BC6C

Mushroom pushbutton heads					
Shape of head	Type of push	Diameter Ø mm/in.	Color of push	Reference	Weight kg/lb
Heads only					
	Spring return	40/1.575	Black	ZB2BC2C	0.045/0.099
			Green	ZB2BC3C	0.045/0.099
			Red	ZB2BC4C	0.045/0.099
			Yellow	ZB2BC5C	0.045/0.099
			Blue	ZB2BC6C	0.045/0.099
		60/2.362	Black	ZB2BR2C	0.055/0.121
			Green	ZB2BR3C	0.055/0.121
			Red	ZB2BR4C	0.055/0.121

XB2B-XA2B_CP22057



ZB2BT4EC

XB2B-XA2B_CP22059



ZB2BS42C

Emergency switching off heads

Shape of head	Type of push	Push Ø (mm)/in.	Color	Reference	Weight kg/lb
Heads only					
	Push-pull	40/1.575	Red	ZB2BT4EC	0.050/0.110
	Turn to release	30/1.181	Black	ZB2BS42C	0.045/0.099
		30/1.181	Red	ZB2BS44C	0.045/0.099
		40/1.575	Red	ZB2BS54C	0.055/0.121
		60/2.362	Red	ZB2BS64C	0.065/0.143

Emergency stop heads (1)

Shape of head	Type of push	Diameter Ø (mm)/in.	Reference	Weight kg/lb
Heads only				
	Push-pull	40/1.575	ZB2BT84C	0.075/0.165
	Turn to release	40/1.575	ZB2BS844C	0.071/0.156

ZB2BS844C_Man_2022



ZB2BS844C

Illuminated pushbutton heads with spring return

Shape of head	Type of push	Color of push	Reference	Weight kg/lb
Heads only				
	Flush	White	ZB2BW31C	0.030/0.066
		Green	ZB2BW33C	0.030/0.066
		Red	ZB2BW34C	0.030/0.066
		Orange	ZB2BW35C	0.030/0.066
		Blue	ZB2BW36C	0.030/0.066
	Projecting	White	ZB2BW11C	0.030/0.066
		Green	ZB2BW13C	0.030/0.066
		Red	ZB2BW14C	0.030/0.066

XB2B-XA2B_CP22098



ZB2BW35C

XB2B-XA2B_CP22094



ZB2BW14C

(1) Emergency Stop pushbuttons should have a maximum of 4 contact blocks, installed in 2 rows only.

Selector switch heads					
Shape of head	Type of operator	Positions Number	Type	Reference	Weight kg/lb
Heads only					
  ZB2BD4C	 Standard handle	2 - stay put		ZB2BD2C	0.045/0.099
		2 - spring return		ZB2BD4C	0.045/0.099
		3 - stay put		ZB2BD3C	0.045/0.099
		3 - spring return from 2 sides		ZB2BD5C	0.045/0.099
		3 - spring return from 1 side		ZB2BD7C	0.045/0.099
  ZB2BJ4C	 Long handle	2 - stay put		ZB2BJ2C	0.045/0.099
		2 - spring return		ZB2BJ4C	0.045/0.099
		3 - stay put		ZB2BJ3C	0.045/0.099
		3 - spring return from 2 sides		ZB2BJ5C	0.045/0.099
		3 - spring return from 1 side		ZB2BJ7C	0.045/0.099
  ZB2BG4C	 Key	2 - stay put, 1 side pull out		ZB2BG2C	0.07/0.154
		2 - stay put, 2 side pull out		ZB2BG4C	0.07/0.154
		2 - spring return, 1 side pull out		ZB2BG6C	0.07/0.154
		3 - stay put, middle pull out		ZB2BG3C	0.07/0.154
		3 - stay put, 2 sides pull out		ZB2BG5C	0.07/0.154
		3 - stay put, 3 sides pull out		ZB2BG0C	0.07/0.154



ZB2BW061C



ZB2BWM31C

Complete light bodies (fixing collar + light block)

Light source	Supply voltage	Type of contact		Color of light source	Reference	Weight
		NO	NC			
	V					kg/lb
Direct Supply						
No bulb No transformer BA 9s	<380 ~ 50/60Hz	1	–	–	ZB2BW061C	0.090/0.198
		–	1	–	ZB2BW062C	0.090/0.198
		2	–	–	ZB2BW063C	0.090/0.198
		1	1	–	ZB2BW065C	0.090/0.198
with BA 9s 24 V ~ bulb	24 ~	1	–	White	ZB2BWB11C	0.090/0.198
		1	–	Green	ZB2BWB31C	0.090/0.198
		–	1	Green	ZB2BWB32C	0.090/0.198
		1	–	Red	ZB2BWB41C	0.090/0.198
		–	1	Red	ZB2BWB42C	0.090/0.198
		1	–	Orange	ZB2BWB51C	0.090/0.198
		–	1	Orange	ZB2BWB52C	0.090/0.198
		1	–	Blue	ZB2BWB61C	0.090/0.198
		–	1	Blue	ZB2BWB62C	0.090/0.198
with BA 9s 24 V ~ bulb	220-230 ~	1	–	White	ZB2BWM11C	0.090/0.198
		1	–	Green	ZB2BWM31C	0.090/0.198
		–	1	Green	ZB2BWM32C	0.090/0.198
		1	–	Red	ZB2BWM41C	0.090/0.198
		–	1	Red	ZB2BWM42C	0.090/0.198
		1	–	Orange	ZB2BWM51C	0.090/0.198
		–	1	Orange	ZB2BWM52C	0.090/0.198
		1	–	Blue	ZB2BWM61C	0.090/0.198

XA2E_CP20053_2



XA2EVB4LC

Pilot lights with integral LED, screw clamp terminal connection					
Shape of head	Supply voltage V	Color of lens	Sold in lots of	Reference	Weight kg/lb
	12 ~	White	10	XA2EVJ1LC	0.025/0.055
		Green	10	XA2EVJ3LC	0.025/0.055
		Red	10	XA2EVJ4LC	0.025/0.055
		Orange	10	XA2EVJ5LC	0.025/0.055
		Blue	10	XA2EVJ6LC	0.025/0.055
		Yellow	10	XA2EVJ8LC	0.025/0.055
	24 ~	White	10	XA2EVB1LC	0.025/0.055
		Green	10	XA2EVB3LC	0.025/0.055
		Red	10	XA2EVB4LC	0.025/0.055
		Orange	10	XA2EVB5LC	0.025/0.055
		Blue	10	XA2EVB6LC	0.025/0.055
		Yellow	10	XA2EVB8LC	0.025/0.055
		Green/Red	5	XA2EVB34LC	0.025/0.055
	30 ~	White	10	XA2EVC1LC	0.025/0.055
		Green	10	XA2EVC3LC	0.025/0.055
		Red	10	XA2EVC4LC	0.025/0.055
		Orange	10	XA2EVC5LC	0.025/0.055
		Blue	10	XA2EVC6LC	0.025/0.055
		Yellow	10	XA2EVC8LC	0.025/0.055
	48 ~	White	10	XA2EVE1LC	0.025/0.055
		Green	10	XA2EVE3LC	0.025/0.055
		Red	10	XA2EVE4LC	0.025/0.055
		Orange	10	XA2EVE5LC	0.025/0.055
		Blue	10	XA2EVE6LC	0.025/0.055
		Yellow	10	XA2EVE8LC	0.025/0.055
	60...63.5 ~	White	10	XA2EVVE1LC	0.025/0.055
		Green	10	XA2EVVE3LC	0.025/0.055
		Red	10	XA2EVVE4LC	0.025/0.055
		Orange	10	XA2EVVE5LC	0.025/0.055
		Blue	10	XA2EVVE6LC	0.025/0.055
		Yellow	10	XA2EVVE8LC	0.025/0.055

XA2E_CP20056_2



XA2EVC6LC

XA2E_CP20054_2



XA2EVE4LC

Note: For information on dimensions, please refer to the www.se.com, Easy Harmony XA2 offer.

Pilot lights with integral LED, screw clamp terminal connection

Shape of head	Supply voltage V	Color of lens	Sold in lots of	Reference	Weight kg/lb
	110 ~	White	10	XA2EVF1LC	0.019/0.041
		Green	10	XA2EVF3LC	0.019/0.041
		Red	10	XA2EVF4LC	0.019/0.041
		Orange	10	XA2EVF5LC	0.019/0.041
		Blue	10	XA2EVF6LC	0.019/0.041
		Yellow	10	XA2EVF8LC	0.019/0.041
	220 ~	White	10	XA2EVMD1LC	0.019/0.041
		Green	10	XA2EVMD3LC	0.019/0.041
		Red	10	XA2EVMD4LC	0.019/0.041
		Orange	10	XA2EVMD5LC	0.019/0.041
		Blue	10	XA2EVMD6LC	0.019/0.041
		Yellow	10	XA2EVMD8LC	0.019/0.041
	220-230 ~	White	10	XA2EVM1LC	0.019/0.041
		Green	10	XA2EVM3LC	0.019/0.041
		Red	10	XA2EVM4LC	0.019/0.041
		Orange	10	XA2EVM5LC	0.019/0.041
		Blue	10	XA2EVM6LC	0.019/0.041
		Yellow	10	XA2EVM8LC	0.019/0.041
		Green/Red	5	XA2EVM34LC	0.019/0.041
	380...400 ~	White	10	XA2EVQ1LC	0.019/0.041
		Green	10	XA2EVQ3LC	0.019/0.041
		Red	10	XA2EVQ4LC	0.019/0.041
		Orange	10	XA2EVQ5LC	0.019/0.041
		Blue	10	XA2EVQ6LC	0.019/0.041
		Yellow	10	XA2EVQ8LC	0.019/0.041

XA2E_CP20055_2



XA2EVM5LC

XA2E_CP20057_2



XA2EVQ8LC

Contact functions

Screw clamp terminal connections

Description	Type of contacts		Sold in lots of	Unit reference	Weight kg/lb
	NO	NC			
Single contact block	1	–	1	ZB2BE101C	0.015/0.033
	–	1	1	ZB2BE102C	0.015/0.033
Single with body/fixing collar	1	–	1	ZB2BZ101C	0.040/0.088
	–	1	1	ZB2BZ102C	0.040/0.088
	2	–	1	ZB2BZ103C	0.055/0.121
	–	2	1	ZB2BZ104C	0.055/0.121
	1	1	1	ZB2BZ105C	0.055/0.121

XB2B-XA2B_CP22123



ZB2BZ104C

Push-push module

Description	Sold in lots of	Reference	Weight kg/lb
Block to convert a spring return into a latching module To be installed before the contact blocks Not compatible with emergency stop, emergency switch off, selector and key switch buttons	5	ZB2BZ21C	0.015/0.033

XB2B-XA2B_CP22127



ZB2BZ21C

Bulbs

Description	Supply voltage V	Color	Sold in lots of	Unit reference	Weight kg/lb
BA 9s	24 ~	White	10	DL1-LED241	0.002/0.0044
		Green	10	DL1-LED243	0.002/0.0044
		Red	10	DL1-LED244	0.002/0.0044
	110 ~	White	1	DL1-LED1101	0.002/0.0044
		Green	1	DL1-LED1103	0.002/0.0044
		Red	1	DL1-LED1104	0.002/0.0044
		Orange	1	DL1-LED1105	0.002/0.0044
		Blue	1	DL1-LED1106	0.002/0.0044
	220 ~	Green	1	DL1-LED2203	0.002/0.0044
		Red	1	DL1-LED2204	0.002/0.0044
		Orange	1	DL1-LED2205	0.002/0.0044
		Blue	1	DL1-LED2206	0.002/0.0044

XB2B-XA2B_CP22133



DL1-LED243



ZB2BZ32C



ZBY02304C

Legend holders

Description	Sold in lots of	Reference	Weight kg/lb
30 x 40 mm for 8 x 27 mm legends	10	ZB2BZ32C	0.001/0.0022
30 x 50 mm for 18 x 27 mm legends	10	ZB2BZ33C	0.001/0.0022

Legends

Description	Marking	Color	Sold in lots of	Reference	Weight kg/lb
8 x 27mm	STOP	Red	10	ZBY02304C	0.0005/0.0011
	ON	Black	10	ZBY02311C	0.0005/0.0011
	OFF-ON	Black	10	ZBY02367C	0.0005/0.0011
	EMERGENCY STOP	Yellow	10	ZBY04330C	0.0005/0.0011
27 x 18 mm	OFF-ON	Black	10	ZBY502367C	0.0005/0.0011
	—	White	10	ZBY5102C	0.0005/0.0011

ZB2BY9330C_Main_2022



ZB2BY9330C

ZB2BZ1605C_2



ZB2BZ1605C

Circular yellow legends for mushroom head pushbuttons

Used for "Emergency stop" function

Diameter Ø (mm)/in.	Marking	Color	Sold in lots of	Reference	Weight kg/lb
60/2.363	"EMERGENCY STOP"	Yellow	10	ZB2BY9330C	0.006/0.0132

Yellow guard

Description	Exclusive use with the following Ø 40mm/1.75 in.	Color	Sold in lots of	Reference	Weight kg/lb
For Emergency stop and off function	Emergency switching	Yellow	1	ZB2BZ1605C	0.009/0.0198
Clear boot for dust	—	Clear	10	ZB2BPAC	0.009/0.0198

Colored boots

Description	Color	For use with	Sold in lots of	Unit reference	Weight kg/lb
Colored boots (can be replaced without dismantling the head)	Black	ZB2BP2C	10	ZBP012	0.003/0.007
	Green	ZB2BP3C	10	ZBP013	0.003/0.007
	Red	ZB2BP4C	10	ZBP014	0.003/0.007
	Yellow	ZB2BP5C	10	ZBP015	0.003/0.007
	Blue	ZB2BP6C	10	ZBP016	0.003/0.007

Annunciator and pilot light associated accessory


Description	Application	Sold in lots of	Unit reference	Weight kg/lb
Bezel tool	Tightening head fixing nut	1	ZB5AZ905	0.016/0.035

Control and signaling units Ø 22

Easy Harmony XB2 metal
Empty control stations for XB2 pushbuttons, switches,
and pilot lights




XALB015C



XALB025C



XALB035C



XALB015YC


Empty control stations					
Description	Level of protection (1)	Dimensions w x h x d mm/in.	Number of cut-outs	Reference	Weight kg/lb
Plastic Light gray cover Dark gray base Single row of contacts Non-illuminated functions and Ø 40 mm/Ø 1.575 in. mushroom heads	IP65	75 x 75 x 50/ 2.96 x 2.96 x 1.97	1	XALB015C	0.102/0.225
		75 x 118 x 50/ 2.96 x 4.65 x 1.97	2	XALB025C	0.132/0.292
		75 x 174 x 50/ 2.96 x 6.85 x 1.97	3	XALB035C	0.179/0.395
Plastic Yellow cover Dark gray base Single row of contacts Non-illuminated functions and Ø 40 mm/Ø 1.575 in. mushroom heads	IP65	75 x 75 x 50/ 2.96 x 2.96 x 1.97	1	XALB015YC	0.102/0.225

(1) The control station achieves an IP65 rating when used with IP65 rated pushbuttons and cabling accessories.

Control and signaling units Ø 22

Easy Harmony XB2 metal
Empty control stations for XB2 pushbuttons, switches,
and pilot lights

Empty control stations (continued)

Description	Level of protection (1)	Dimensions w x h x d mm/in.	Number of cut-outs	Reference	Weight kg/lb
 Plastic Light gray cover Dark gray base for illuminated functions, mushroom heads or double-row contact blocks	IP65	75 x 75 x 70/ 2.96 x 2.96 x 2.76	1	XALB017C	0.129/0.285
 Plastic Light gray cover Dark gray base for illuminated functions, mushroom heads or double-row contact blocks	IP65	75 x 118 x 70/ 2.96 x 4.65 x 2.76	2	XALB027C	0.159/0.351
 Plastic Light gray cover Dark gray base for illuminated functions, mushroom heads or double-row contact blocks	IP65	75 x 174 x 70/ 2.96 x 6.85 x 2.76	3	XALB037C	0.214/0.472
 Plastic Yellow cover Dark gray base for illuminated functions, mushroom heads or double-row contact blocks	IP65	75 x 75 x 70/ 2.96 x 2.96 x 2.76	1	XALB017YC	0.129/0.285

(1) The control station achieves an IP65 rating when used with IP65 rated pushbuttons and cabling accessories.

Schneider
Electric

mySchneider, your personalized digital experience

Access an all-in-one customized online experience and benefit from tailored business services, resources, and tools to efficiently support your business operations.

- **Efficiency:** In just a few clicks, find all the information and support you need to get the job done.
- **Simplicity:** Use a single login to access all business services, in one place, available 24/7. You no longer need to log in to multiple platforms.
- **Personalization:** Benefit from content, tools, and business services tailored to your activity, and customize your landing page based on your preferences.

Watch the How-to Videos



Order management

- > [Select Products and Add to Cart](#)
- > [Check for Products' Price and Availability](#)
- > [Order Products with Generic Commercial References](#)




Product information

- > [Find a Product Data Sheet and Related Documents](#)
- > [Select Products and Add to Cart](#)
- > [Stay Up to Date on the Status of My Products](#)



Support

- > [Get Quicker Answers Thanks to Online Support](#)



Training

- > [Access Trainings Dedicated to My Activity](#)

"On mySchneider, I find all the product and training information I need."

[Create your account](#)

Life Is On

Schneider
Electric

Legal information

The information provided in this Catalog contains description of Schneider Electric products, solutions and services ("Offer") with technical specifications and technical characteristics of the performance of the corresponding Offer.

The content of this document is subject to revision at any time without notice due to continued progress in methodology, design and manufacturing.

To the extent permitted by applicable law, no responsibility or liability is assumed by Schneider Electric and its subsidiaries for any type of damages arising out of or in connection with (i) informational content of this Catalog not conforming with or exceeding the technical specifications, or (ii) any error contained in this Catalog, or (iii) any use, decision, act or omission made or taken on basis of or in reliance on any information contained or referred to in this Catalog.


SCHNEIDER ELECTRIC MAKES NO WARRANTY OR REPRESENTATION OF ANY KIND, WHETHER EXPRESS OR IMPLIED, AS TO WHETHER THIS CATALOG OR ANY INFORMATION CONTAINED THEREIN SUCH AS PRODUCTS AND SERVICES WILL MEET REQUIREMENTS, EXPECTATIONS OR PURPOSE OF ANY PERSON MAKING USE THEREOF.

Schneider Electric brand and any trademarks of Schneider Electric and its subsidiaries referred to in this Catalog are property of Schneider Electric or its subsidiaries. All other brands are trademarks of their respective owners.

This Catalog and its content are protected under applicable copyright laws and provided for informative use only. No part of this Catalog may be reproduced or transmitted in any form or by any means (electronic, mechanical, photocopying, recording, or otherwise), for any purpose, without the prior written permission of Schneider Electric.

Copyright, intellectual, and all other proprietary rights in the content of this Catalog (including but not limited to software, audio, video, text, and photographs) rests with Schneider Electric or its licensors. All rights in such content not expressly granted herein are reserved. No rights of any kind are licensed or assigned or shall otherwise pass to persons accessing this information.

Life Is On



Learn more about our products at
www.se.com

Design: Schneider Electric
Photos: Schneider Electric

Schneider Electric Industries SAS

Head Office
35, rue Joseph Monier - CS 30323
F-92500 Rueil-Malmaison Cedex
France

DIA5ED2220401EN
November 2024 - V2.0