

IOA FEED-THRU/EX - Feed-through plug



2906598

<https://www.phoenixcontact.com/in/products/2906598>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Feed-through terminal block for VIP I/O-Marshalling base elements for conveying field signals to or from the I/O system.

Product description

Feed-through terminal block for conveying field signals to or from the I/O system. The module is installed on a corresponding VIP I/O-Marshalling base element by means of plug-in contact. Installation in zone 2, "ec" type of protection is permitted.

Your advantages

- Two-stage progressive release

Commercial data

Item number	2906598
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	CK8
Product key	DK115Z
Catalog page	Page 554 (C-5-2017)
GTIN	4055626171784
Weight per piece (including packing)	53.82 g
Weight per piece (excluding packing)	53.2 g
Customs tariff number	85389099
Country of origin	US

Technical data

Product properties

Product type	Interface module
Product family	VIP I/O-Marshalling
Set comprises	1433798 IOA FEED-THRU/EX/BULK PACK
No. of channels	1
Operating mode	100% operating factor

Insulation characteristics

Overvoltage category	II
Pollution degree	2

Electrical properties

Max. operating voltage $U_{\max}$	30 V
Max. permissible current	1 A
Nominal voltage U_N	24 V DC
Max. current carrying capacity per branch	1 A

Output data

Nominal supply voltage	24 V DC
Continuous load current	1 A

Connection data

Control circuits

Connection method	Pin strip
Number of connections	1
Number of positions	13

Ex data

Safety data

Input voltage U_i	30 V
Input current I_i	1 A
Inductance L_i	0 mH
Capacitance C_i	0 μ F
Max. output voltage U_o	U_i
Max. output current I_o	I_i
Max. output power P_o	P_i

Signaling

Status display	no
Status display present	No

IOA FEED-THRU/EX - Feed-through plug



2906598

<https://www.phoenixcontact.com/in/products/2906598>

Dimensions

Item dimensions

Width	10.3 mm
Height	64.2 mm
Depth	72.9 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 75 °C
Ambient temperature (storage/transport)	-40 °C ... 75 °C
Altitude	< 2000 m
Permissible humidity (operation)	0 % ... 95 % (non-condensing)

Approvals

ATEX

Identification	⚡ II 3G Ex nA IIC T4 Gc
Certificate	CSANe 21ATEX4128X

IECEX

Identification	Ex nA IIC T4 Gc
Certificate	IECEX CSAE 21.0004X

UKEX

Identification	⚡ II 3G Ex nA IIC T4 Gc
Certificate	PxCIF23UKEX2906598X

UL, USA/Canada

Identification	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2, IIC T4

CSA, USA/Canada

Identification	Class I, Div. 2, Groups A, B, C, D T4
	Class I, Zone 2, AEx nA IIC T4 Gc
	Ex nA IIC T4 Gc

Standards and regulations

Standards/regulations	IEC 60664
	DIN EN 50178

IOA FEED-THRU/EX - Feed-through plug



2906598

<https://www.phoenixcontact.com/in/products/2906598>

Mounting

Mounting position	any
-------------------	-----

IOA FEED-THRU/EX - Feed-through plug


2906598

<https://www.phoenixcontact.com/in/products/2906598>




Drawings

Dimensional drawing



Circuit diagram



IOA FEED-THRU/EX - Feed-through plug



2906598

<https://www.phoenixcontact.com/in/products/2906598>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/2906598>

Functional Safety

Approval ID: PHO 16-09-035



IECEx

Approval ID: IECEx CSAE 21.0004X



CSA

Approval ID: 80071103



CSAus

Approval ID: 80071103



ATEX

Approval ID: CSANe 21ATEX4128X



cULus Listed

Approval ID: E196811-201707007

cULus Listed

cCSAus

IOA FEED-THRU/EX - Feed-through plug

2906598

<https://www.phoenixcontact.com/in/products/2906598>



Classifications

ECLASS

ECLASS-11.0	27141152
ECLASS-12.0	27141152
ECLASS-13.0	27141152

ETIM

ETIM 9.0	EC002780
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

IOA FEED-THRU/EX - Feed-through plug



2906598

<https://www.phoenixcontact.com/in/products/2906598>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

IOA FEED-THRU/EX - Feed-through plug



2906598

<https://www.phoenixcontact.com/in/products/2906598>

Mandatory accessories

VIP/S/MC/BASE 1-8/L/EX - Base module

2906596

<https://www.phoenixcontact.com/in/products/2906596>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. With the COMBICON connector, compatible with the Honeywell C300 and RUSIO series. Marking for channels 1–8.

VIP/S/MC/BASE 9-16/L/EX - Base module

2906630

<https://www.phoenixcontact.com/in/products/2906630>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. With the COMBICON connector, compatible with the Honeywell C300 and RUSIO series. Marking for channels 9–16.

IOA FEED-THRU/EX - Feed-through plug

2906598

<https://www.phoenixcontact.com/in/products/2906598>



VIP/S/MC/BASE 17-24/L/EX - Base module

2907024

<https://www.phoenixcontact.com/in/products/2907024>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. With the COMBICON connector, compatible with the Honeywell C300 and RUSIO series. Marking for channels 17–24.

VIP/S/MC/BASE 25-32/L/EX - Base module

2907025

<https://www.phoenixcontact.com/in/products/2907025>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. With the COMBICON connector, compatible with the Honeywell C300 and RUSIO series. Marking for channels 25–32.

IOA FEED-THRU/EX - Feed-through plug

2906598

<https://www.phoenixcontact.com/in/products/2906598>



VIP/S/MC/BASE 1-8/L/C/EX - Base module

2907186

<https://www.phoenixcontact.com/in/products/2907186>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. With the COMBICON connector, compatible with the Honeywell C300 and RUSIO series. Marking for channels 1–8 and painting.

VIP/S/MC/BASE 9-16/L/C/EX - Base module

2907187

<https://www.phoenixcontact.com/in/products/2907187>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. With the COMBICON connector, compatible with the Honeywell C300 and RUSIO series. Marking for channels 9–16 and painting.

IOA FEED-THRU/EX - Feed-through plug

2906598

<https://www.phoenixcontact.com/in/products/2906598>



VIP/S/MC/BASE 17-24/L/C/EX - Base module

2907209

<https://www.phoenixcontact.com/in/products/2907209>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. With the COMBICON connector, compatible with the Honeywell C300 and RUSIO series. Marking for channels 17-24 and painting.

VIP/S/MC/BASE 25-32/L/C/EX - Base module

2907210

<https://www.phoenixcontact.com/in/products/2907210>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. With the COMBICON connector, compatible with the Honeywell C300 and RUSIO series. Marking for channels 25-32 and painting.

IOA FEED-THRU/EX - Feed-through plug

2906598

<https://www.phoenixcontact.com/in/products/2906598>



VIP/S/D25M/BASE 1-8/L/C/EX - Base module

2906595

<https://www.phoenixcontact.com/in/products/2906595>



8-channel VIP I/O marshalling base element for universal use. All connections as screw connection technology. This module with the D-SUB 25 connector is pin compatible with the Foxboro I/A series DCS.

VIP/MSTB/D50M/BASE/16CH/CX/EX - Base module

2908788

<https://www.phoenixcontact.com/in/products/2908788>



16-channel VIP I/O marshalling base element for universal use. Plug-in field and supply terminals available as accessories. Either with screw or Push-in connection technology. Compatible with the Tricon CX DCS series (D-SUB 50).

IOA FEED-THRU/EX - Feed-through plug

2906598

<https://www.phoenixcontact.com/in/products/2906598>



BASE-MSTB/D37M/16CH/EX - Base module

1065476

<https://www.phoenixcontact.com/in/products/1065476>



16-channel VIP I/O marshalling base element with 37-pos. D-SUB connector for universal use. Plug-in field and supply terminals available as accessories. Either with screw or Push-in connection technology.

Accessories

UC-TM 6 - Marker for terminal blocks

0818085

<https://www.phoenixcontact.com/in/products/0818085>



Marker for terminal blocks, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 6.2 mm, Number of individual labels: 80, text field height: 10.5 mm, text field width: 5.6 mm

IOA FEED-THRU/EX - Feed-through plug

2906598

<https://www.phoenixcontact.com/in/products/2906598>



UC-TM 6 BU - Marker for terminal blocks

0818344

<https://www.phoenixcontact.com/in/products/0818344>



Marker for terminal blocks, Sheet, blue, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 6.2 mm, Number of individual labels: 80, text field height: 10.5 mm, text field width: 5.6 mm

ZB 5,08:UNBEDRUCKT - Zack marker strip

0809793

<https://www.phoenixcontact.com/in/products/0809793>



Zack marker strip, Strip, white, unlabeled, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, for terminal block width: 5.08 mm, Number of individual labels: 10, text field height: 10.5 mm, text field width: 4.98 mm

IOA FEED-THRU/EX - Feed-through plug

2906598

<https://www.phoenixcontact.com/in/products/2906598>



B-STIFT - Marker pen

1051993

<https://www.phoenixcontact.com/in/products/1051993>



Marker pen, for manual labeling of unprinted Zack strips, smear-proof and waterproof, line thickness 0.5 mm

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in