



PRODUCT-DETAILS

SAMHL25/25M**25MM SS-TPE COAT CONDUIT 25M - WH****General Information**

Extended Product Type:	SAMHL25/25M
Product ID:	7TCA296030R0443
EAN:	5020963801525
Catalog Description:	25MM SS-TPE COAT CONDUIT 25M - WH
Long Description:	Liquidtight. Anti-Microbial Conduit, Conduit Size - Metric 25 Millimeters / US Trade Size 3/4 Inch, Outside Diameter 26.7mm, Inside Diameter 21.0mm, Static Bend Radius 110mm, IP40-IP69 Rating, Galvanised Steel Core, String Packed and Thermoplastic Jacket, Reel Length 25 Meters, White
Display Name:	SAMHL25/25M

Additional Information

Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Suitable for indoor splash zone areas or food processing equipment

Ordering

EAN:	5020963801525
UPC:	786210212982

Dimensions

Outside Diameter:	26.4 mm
--------------------------	---------

Technical

Number of Batteries:	0
Color:	White
Material:	Galvanised Steel Core, String Packed and Thermoplastic Jacket

Environmental

WEEE Category:	Product Not in WEEE Scope
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units:	1 piece
Package Level 1 EAN:	5020963801525
Package Level 1 Height:	10 in 254 mm
Package Level 1 Depth / Length:	16 in 406 mm
Package Level 1 Width:	16 in 406 mm

Certificates and Declarations

Declaration of Conformity - CE:	9AKK107492A9618
RoHS Declaration:	9AKK107992A8994
REACH Declaration:	9AKK107992A8994

External Classifications and Standards

ETIM 8:	EC001179 - Protective metallic hose
ETIM 9:	EC001179 - Protective metallic hose
UNSPSC:	39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

