



# LC1D326BL

TeSys D contactor - 3P(3 NO) - AC-3 - <= 440 V 32 A - 24 V DC coil



[Download your LC1D326BL datasheet](#)



[Characteristics](#) | [Documents & Downloads](#)

## Main

Hide

<b>Range</b>	TeSys
<b>Product name</b>	TeSys D
<b>Product or component type</b>	Contactors
<b>Device short name</b>	LC1D
<b>Contactors application</b>	Motor control Resistive load
<b>Utilisation category</b>	AC-1 AC-3
<b>Poles description</b>	3P
<b>Pole contact composition</b>	3 NO
<b>[Ue] rated operational voltage</b>	<= 690 V AC 25...400 Hz for power circuit <= 300 V DC for power circuit
<b>[Ie] rated operational current</b>	32 A (<= 60 °C) at <= 440 V AC AC-3 for power circuit 50 A (<= 60 °C) at <= 440 V AC AC-1 for power circuit
<b>Motor power kW</b>	15 kW at 380...400 V AC 50/60 Hz 7.5 kW at 220...230 V AC 50/60 Hz 18.5 kW at 500 V AC 50/60 Hz 18.5 kW at 660...690 V AC 50/60 Hz 15 kW at 415...440 V AC 50/60 Hz
<b>Motor power hp</b>	2 hp at 115 V AC 50/60 Hz for 1 phase motors 5 hp at 230/240 V AC 50/60 Hz for 1 phase motors 7.5 hp at 200/208 V AC 50/60 Hz for 3 phases motors 10 hp at 230/240 V AC 50/60 Hz for 3 phases motors 20 hp at 460/480 V AC 50/60 Hz for 3 phases motors 30 hp at 575/600 V AC 50/60 Hz for 3 phases motors
<b>Control circuit type</b>	DC low consumption
<b>Control circuit voltage</b>	24 V DC
<b>Auxiliary contact composition</b>	1 NO + 1 NC
<b>[Uimp] rated impulse withstand voltage</b>	6 kV conforming to IEC 60947
<b>Oversvoltage category</b>	III
<b>[Ith] conventional free air thermal current</b>	50 A at <= 60 °C for power circuit 10 A at <= 60 °C for signalling circuit
<b>Irms rated making capacity</b>	550 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1
<b>Rated breaking capacity</b>	550 A at 440 V for power circuit conforming to IEC 60947
<b>[Icw] rated short-time withstand current</b>	138 A <= 40 °C 1 min power circuit 260 A <= 40 °C 10 s power circuit 430 A <= 40 °C 1 s power circuit 60 A <= 40 °C 10 min power circuit 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit
<b>Associated fuse rating</b>	63 A gG at <= 690 V coordination type 1 for power circuit 63 A gG at <= 690 V coordination type 2 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1
<b>Average impedance</b>	2 mOhm at 50 Hz - Ith 50 A for power circuit
<b>[Ui] rated insulation voltage</b>	600 V for power circuit certifications CSA

	600 V for power circuit certifications UL 690 V for power circuit conforming to IEC 60947-4-1 690 V for signalling circuit conforming to IEC 60947-1 600 V for signalling circuit certifications CSA 600 V for signalling circuit certifications UL
<b>Electrical durability</b>	1.65 Mcycles 32 A AC-3 at $U_e \leq 440$ V 1.4 Mcycles 50 A AC-1 at $U_e \leq 440$ V
<b>Power dissipation per pole</b>	2 W AC-3 5 W AC-1
<b>Protective cover</b>	With
<b>Mounting support</b>	Plate Rail
<b>Standards</b>	EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 CSA C22.2 No 14
<b>Product certifications</b>	BV CCC CSA DNV GL GOST RINA UL LROS
<b>Connections - terminals</b>	Control circuit : lugs-ring terminals - external diameter: 8 mm Power circuit : lugs-ring terminals - external diameter: 10 mm
<b>Tightening torque</b>	Control circuit : 1.7 N.m - on lugs-ring terminals - with screwdriver flat $\varnothing$ 6 mm screw : M3.5 Control circuit : 1.7 N.m - on lugs-ring terminals - with screwdriver Philips No 2 screw : M3.5 Power circuit : 2.5 N.m - on lugs-ring terminals - with screwdriver flat $\varnothing$ 8 mm screw : M4 Power circuit : 2.5 N.m - on lugs-ring terminals - with screwdriver Philips No 2 screw : M4
<b>Operating time</b>	65.45...88.55 ms closing 20...30 ms opening
<b>Safety reliability level</b>	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1
<b>Mechanical durability</b>	30 Mcycles
<b>Operating rate</b>	3600 cyc/h at $\leq 60$ °C

## Complementary Hide


<b>Coil technology</b>	Built-in bidirectional peak limiting diode suppressor
<b>Control circuit voltage limits</b>	0.1...0.3 $U_c$ at 60 °C drop-out 0.8...1.25 $U_c$ at 60 °C operational
<b>Time constant</b>	40 ms
<b>Inrush power in W</b>	2.4 W at 20 °C
<b>Hold-in power consumption in W</b>	2.4 W at 20 °C
<b>Auxiliary contacts type</b>	Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1
<b>Signalling circuit frequency</b>	25...400 Hz
<b>Minimum switching current</b>	5 mA for signalling circuit
<b>Minimum switching voltage</b>	17 V for signalling circuit
<b>Non-overlap time</b>	1.5 ms on de-energisation (between NC and NO contact) 1.5 ms on energisation (between NC and NO contact)
<b>Insulation resistance</b>	> 10 MOhm for signalling circuit

## Environment Hide

<b>IP degree of protection</b>	IP2x front face conforming to IEC 60529
<b>Protective treatment</b>	TH conforming to IEC 60068-2-30
<b>Pollution degree</b>	3

<b>Ambient air temperature for operation</b>	-5...60 °C
<b>Ambient air temperature for storage</b>	-60...80 °C
<b>Permissible ambient air temperature around the device</b>	-40...70 °C at U <sub>c</sub>
<b>Operating altitude</b>	3000 m without derating in temperature
<b>Fire resistance</b>	850 °C conforming to IEC 60695-2-1
<b>Flame retardance</b>	V1 conforming to UL 94
<b>Mechanical robustness</b>	Vibrations contactor open 2 G <sub>n</sub> , 5...300 Hz Vibrations contactor closed 4 G <sub>n</sub> , 5...300 Hz Shocks contactor closed 15 G <sub>n</sub> for 11 ms Shocks contactor open 8 G <sub>n</sub> for 11 ms
<b>Height</b>	85 mm
<b>Width</b>	45 mm
<b>Depth</b>	101 mm
<b>Product weight</b>	0.535 kg

### Offer Sustainability [-] Hide

<b>Sustainable offer status</b>	Green Premium product
<b>RoHS (date code: YYWW)</b>	Compliant - since 0719 - Schneider Electric declaration of conformity
<b>REACH</b>	Reference not containing SVHC above the threshold
<b>Product environmental profile</b>	Available  <a href="#">download Product environmental</a>
<b>Product end of life instructions</b>	Need no specific recycling operations

### Contractual warranty [-] Hide

<b>Period</b>	18 months
---------------	-----------