

XVC6B1KOQ

Monolithic precabled tower light, Harmony XVC, plastic, red, 60mm, base mounting, steady, body silver, IP54, 24V AC DC

Main

Range of product	Harmony XVC6
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	1 illuminated unit
Sound signalling	Without
Mounting diameter	60 mm
Component name	XVC
Light source	LED steady red
[Us] rated supply voltage	24 V
Supply circuit type	AC/DC

Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover
Product mounting	On base
Cable cross section	0.33 mm ²
AWG gauge	AWG 22
Cable length	850 mm
Marking	CE
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	25 mA
Flashing frequency	1 Hz
Net weight	0.2 kg
Height	120.8 mm

Environment

Standards	EN/IEC 61000-6-4 EN/IEC 61000-6-3 EN/IEC 61000-6-2
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
Electrical shock protection class	Class II conforming to EN/IEC 61140
IP degree of protection	IP54 flat surface installation conforming to EN/IEC 60529

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins