

Linetrimmer LXT®

DUR189

18V • 4 000 - 6 000 min⁻¹ • 300 mm

Brushless trimmer with adjustable shaft and auto-speed control for trimming green spaces

An efficient brushless line trimmer with a loop handle. An adjustable shaft, low vibration and good ergonomics ensure a good user experience. Cuts with two 2 mm lines and there is three different speed options or an automatic speed control for adjusting speed in line with load.



LXT BL ADT
MOTOR

Technical specifications

Nominal Battery Voltage	18 V
No load speed	4000 / 5000 / 6000 min ⁻¹
Cutting width	255 / 300 mm
Tool weight with battery	3,0 - 3,3 kg
Nylon line- Diameter	2,0 mm
Sound Pressure Level (L _{pA})	78 dB(A)
Noise Uncertainty (K Factor)	2 dB(A)
Product Dimensions (L x W x H):	1618 x 258 x 396 mm
Brushless Motor	✓
Voltage LXT	✓
Spindle Thread	M8 x 1,25 RH
Handle Type	O
Vibration Level, Nyloncord	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Nyloncord	1,5 m/s ²
Vibration Level, Plastic 3-Blade	≤ 2,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Better manoeuvrability regardless of user's size by telescopic pipe
- Ergonomically designed new loop handle fits comfortably in user's hand
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

125516-5

Band assembly



191D92-5

Trimmer Head 2,0 mm, M8 x 1,25 RH



198971-4

Trimmer Head 2,0 mm, M8 x 1.25 RH



Other

User manual

Parts drawing