



687-584 - ALWAYS 300613

3006-13

Type 13: Carbon
Steel balls & housing

| | |
|---|-----------------------------------|
| Max Dynamic Loading (Kg) LOAD BALL UP | 25 |
| Max Dynamic Loading (Kg) LOAD BALL DOWN | 10 |
| Weight (Kg) | 0.087 |
| Load Ball Diameter Ø (mm) | 19 |
| Fixing Holes | 3 |
| Fixing Methods | Flange |
| Dimension A - Max Diameter (mm) | 61 |
| Dimension B - Working Height of Ball (mm) | 10 |
| Dimension D - Body Diameter (mm) | 29.1 +/- 0.2 |
| Dimension E - Under Flange to Base (mm) | 12 |
| Dimension F - Flange Thickness (mm) | 3.2 |
| Dimension G - PCD or Centres of Fixing Holes (mm) | 44.5 +/- 0.2 |
| Dimension H - Hole Diameter of Fixing Holes (mm) | 5.1 |
| Dimension I / O - Seating Hole Diameter (mm) | 30 |
| Load Ball Material | Carbon Steel |
| Support Ball Material | Carbon Steel |
| Unit Housing Material | Carbon Steel - Bright Zinc Plated |