



Main

Network rated voltage	400 V AC 50 Hz 415 V AC 50 Hz
Reactive power rating	16 kvar
Operating mode	Automatic
Range	PowerLogic
Device short name	automatic capacitor bank
Product or component type	Capacitor bank

Complementary

Network pollution level	Low polluted
[Gh/Sn] harmonic pollution rate	15...25 %
[THDU] total harmonic distortion of voltage	3...4 %
Power per step	3 kvar
Step composition	3 + 2x6.25
Location of connection	Bottom
Controller type	PowerLogic PFC Controller VPL6
Capacitor technology	PowerLogic PFC Capacitor
Poles description	3P
Capacitance tolerance	- 5 % to 10 %
[Ui] rated insulation voltage	500 V
[Uimp] rated impulse withstand voltage	6 kV
Maximum permissible voltage	1.1 x Un (8 hours over 24 hours) conforming to IEC 60831
[Imp] maximum permanent current	Capacitor: 1.8 x In at 480 V conforming to IEC 60831 Battery: 1.43 x In at 400 V conforming to IEC 61439-2 Battery: 1.19 x In at 415 V conforming to IEC 61439-2
Main incomer protection	Circuit breaker protection
Breaking capacity	Icu 15 kA
Step protection type	Overload: harmonic control from PowerLogic PFC Controller Short-circuit: main circuit breaker
Accessibility for operation	Front
Colour	Grey (RAL 7035)
Maximum weight	57 kg
Height	650 mm
Width	450 mm
Depth	250 mm
Provided equipment	Auxiliary transformer
Internal voltage transformer	400/230 V - 100 VA
Function available	Alarm contact GenSet shedding contact

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	IEC 61439-1 IEC 61921 IEC 61439-2
Product certifications	CE[RETURN]EAC[RETURN]ASEFA
Mounting location	Indoor
IP degree of protection	Environment: IP31 Safety: IPxx B
IK degree of protection	IK10
Relative humidity	0...95 %
Operating altitude	<= 2000 m
Ambient air temperature for operation	-5...45 °C
Average ambient air temperature for operation	35 °C (annual) 45 °C (over 24 hours)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Logistical informations

Country of origin	ES
-------------------	----