




Connectors > Automotive Connectors > Seals & Cavity Plugs



Connector Seal Type: **Single Wire Seal (SWS)**
Cavity Diameter: **8.05 mm [.317 in]**
Accepts Cable Insulation Diameter Range: **2.6 – 3.4 mm [.102 – .134 in]**
Seal Material: **Silicone**
Resistance to Hydrocarbons: **Poor**

Features

Product Type Features

Connector Seal Type	Single Wire Seal (SWS)
---------------------	------------------------

Body Features

Seal Material	Silicone
Primary Product Color	Yellow

Dimensions

Cavity Diameter	8.05 mm[.317 in]
Accepts Cable Insulation Diameter Range	2.6 – 3.4 mm[.102 – .134 in]

Usage Conditions

Operating Temperature (Max)	65 °C, 70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C [149 °F][158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F]
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Industry Standards

UL Flammability Rating	None
------------------------	------

Other

Resistance to Hydrocarbons	Poor
Shore A Hardness	40



Contains Lubricant	Yes
--------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2022 (223) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Econoseal



Automotive Connector Caps & Covers (1)



Automotive Connector Locks & Position Assurance(25)



Automotive Housings(60)



Automotive Seals & Cavity Plugs(17)



Automotive Terminals(47)

Insertion & Extraction Tools(7)

Other Automotive Connector Accessories(5)

PCB Headers & Receptacles(4)

Customers Also Bought

TE Part #1746865-1
TH/.025 CONNECTOR SYSTEM, HOUSING

TE Part #1355044-1
TIMER, CONNECTOR HOUSING

TE Part #3-1633730-5
CRIMPER, WIRE F .039F

TE Part #1-2361027-1
PLUG ASSY, KEY A, CPA, HVA280-2PHI, HB

TE Part #1-453818-0
CRIMPER, WIRE-.055 WIDE F

TE Part #657865-2
ANVIL

Documents

Product Drawings
2.0MM CABLE SEAL HC SILIC

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_347713-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_347713-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_347713-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

347713-1

Automotive Seals & Cavity Plugs, Single Wire Seal (SWS), Cavity Diameter .317 in [8.05 mm], Silicone, Poor, 40, Contains Lubricant, Yellow, Econoseal

