



Brand of NTN corporation



# Technical data

## 7210CG1DUJ74

High precision angular contact ball bearings



### VISUAL (S)



### NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

# 7210CG1DUJ74

High precision angular contact ball bearings

## PRODUCT DEFINITION

<b>Brand</b>	SNR
<b>d - Internal diameter</b>	50 mm
<b>D - External diameter</b>	90 mm
<b>B - Bearing/Inner ring width</b>	20 mm
<b>d1 - External diameter inner ring</b>	62,45 mm
<b>D1 - Inner diameter outer ring</b>	76,85 mm
<b>D2 - Inner diameter outer ring</b>	82,83 mm
<b>a - Charge load application point</b>	19 mm
<b>- Contact angle</b>	15 °
<b>rs - Min fillet radius</b>	1,1 mm
<b>r1s - Min fillet radius</b>	0,6 mm
<b>Precision class</b>	P4
<b>Mass</b>	0,486 kg

## PRODUCT PERFORMANCE

<b>C - Dynamic load</b>	44800000 mN
<b>C0 - Static load</b>	34000000 mN
<b>Cu - Fatigue limit load</b>	1820000 mN
<b>f0 - Coefficient</b>	14.56
<b>Axial displacement K Factor</b>	1.21
<b>Preload level</b>	7
<b>Preload value</b>	240000 mN
<b>Axial rigidity</b>	75 N/μm
<b>Radial rigidity</b>	421 N/μm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

# 7210CG1DUJ74

High precision angular contact ball bearings

## PRODUCT PERFORMANCE

<b>Tmin - Min operating temperature</b>	243,15 °K
<b>Tmax - Max operating temperature</b>	393,15 °K
<b>N lim - Oil lubrication limit speed</b>	144000 °/s
<b>N lim - Grease lubrication limit speed</b>	90000 °/s

## BEARING FREQUENCIES

<b>BPFO - Over rolling frequency on outer ring (60 rpm)</b>	6.186 Hz
<b>BPFI - Over rolling frequency on inner (60 rpm)</b>	8.814 Hz
<b>BSF - Over rolling frequency on rolling element (60 rpm)</b>	5.343 Hz
<b>BRF - Rotational frequency - rolling element (60 rpm)</b>	2.672 Hz
<b>FTF - Rotational frequency - cage (60 rpm)</b>	0.412 Hz

## ABUTMENT

<b>da min - Min shoulder diameter IR</b>	57 mm
<b>db min - Min IR shoulder diameter</b>	57 mm
<b>Da max - Max shoulder diameter OR</b>	83 mm
<b>Db max - Max OR shoulder diameter</b>	83 mm
<b>r1a - Max fillet radius</b>	0,6 mm
<b>ra max - Max shaft &amp; housing fillet radius</b>	1 mm



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

### INDUSTRY CALCUL FACTORS

#### Equivalent dynamic radial load

$$P = X \cdot Fr + Y \cdot Fa$$

Series	e	Single or DT bearing arrangement				DB or DF arrangement					
		Fa / Fr ≤ e		Fa / Fr > e		Fa / Fr ≤ e		Fa / Fr > e			
		X	Y	X	Y	X	Y	X	Y		
70 (NTN & SNR) 72 (NTN & SNR) 78 (NTN) 79 (NTN) 719 (SNR)	15°	0.178	0.38	1	0	0.44	1.47	1	0.72	1.65	2.39
		0.357	0.4				1.4			1.57	2.28
		0.714	0.43				1.3			1.46	2.11
		1.07	0.46				1.23			1.38	2
		1.43	0.47				1.19			1.34	1.93
		2.14	0.5				1.12			1.26	1.82
		3.57	0.55				1.02			1.14	1.66
		5.35	0.56				1			1.12	1.63
	7.14	0.56	1	1.12	1.63						
	25°	0.68	0.41	0.87	0.92	0.67	1.41				
30°	0.8	0.39	0.76	0.78	0.63	1.24					

#### Equivalent static radial load

$$P_0 = X_0 \cdot Fr + Y_0 \cdot Fa$$

Series	e	Single or DT bearing arrangement		DB or DF arrangement	
		X <sub>0</sub>	Y <sub>0</sub>	X <sub>0</sub>	Y <sub>0</sub>
70 (NTN & SNR) 72 (NTN & SNR) 78 (NTN) 79 (NTN) 719 (SNR)	15°	0.5	0.46	1	0.92
	25°		0.38		0.76
	30°		0.33		0.66

For single or DT bearing arrangement :

If  $P_0 < Fr$ , then use  $P_0 = Fr$



**NTN Europe**

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15