

Product datasheet

Specifications



APC Smart-UPS On-Line, 5kVA/5kW, Rack/Tower, 230V, 2x IEC C13+1x IEC C19+Hard wire 3-wire (H+N+E) outlets, Network Card, W/O rail kit

SRTG5KXLI

Overview

Lead time	Usually in Stock
-----------	------------------

Main


Main Input Voltage	230 V
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	5000 W
rated power in VA	5000 VA
output connection type	2 IEC 60320 C13 1 IEC 60320 C19
Output connector type	Hard wire 3-wire (1P + N + E) 1
Number of rack unit	4U
Provided equipment	1 x USB cable 1 x RJ45 cable 1 x rack mounting brackets 1 x stabilization/wall mounting feet 1 x installation manual 1 x C13-C14 power cord
Range of product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery type	Lead-acid battery
Battery voltage	+/- 96 V
Extended runtime	1
Number of battery filled slots	2
Number of battery free slots	0
Battery recharge time	4 h
Number of battery replacement quantity	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Battery life	3...5 year(s)
Replacement battery	APCRBC170 
Battery charger power	239 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
UPS type	Double conversion online

Physical

Colour	Black (RAL 9005)
Height	17.5 cm
Width	44 cm
Depth	62 cm
Net weight	55.9 kg
Mounting preference	Lower
Mounting mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes
Mounting position	Horizontal

Input

Maximum input current	30 A
Switching current capacity	40 A
Input voltage limits	160...285 V full load 100...285 V half load
Number of input connectors	1 hard wire 3-wire (1P + N + E)
Network frequency	40...70 Hz auto-sensing

Output

Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2 %
Maximum configurable power in VA	5000 VA
Maximum configurable power in W	5000 W
Wave type	Sine wave
Efficiency	93.5 %
Output frequency	50/60 Hz +/- 4 Hz sync to mains
Additional information	Configurable for 220 : 230 or 240 nominal output voltage

Conformance

Product certifications	CE UKCA TISI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	55 dBA
Heat dissipation	1108.95 Btu/h
Operating altitude	0...3000 m
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0...15000 m
IP degree of protection	IP20
Relative humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Emergency power off	Yes
Preinstalled device	Network management card 3 with environmental monitoring
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	27.5 cm
Package 1 Width	79 cm
Package 1 Length	59 cm
Package 1 Weight	61.8 kg


Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---


Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)



[How we assess product sustainability >](#)

<div>Environmental footprint</div>	
Environmental Disclosure	Product Environmental Profile

Use Better

<div>Materials and Substances</div>	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	A64c500c-f72a-458b-8faa-8175a94429fe
REACH Regulation	REACH Declaration

Use Again

<div>Repack and remanufacture</div>	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	No
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins