愛TDK

SMD Inductors(Coils) For Power Line(Wound, Magnetic Shielded)

Conformity to RoHS Directive

RLF Series RLF12560

Accompanying large current power supplies, these inductors have secured efficient characteristics by improving its magnetic circuit based on existing products. These products meet resistance reducing and current enlargement.

FEATURES

- Comparing with existing products(RLF12545), DC current superimposition characteristic has improved. Especially, inductance rises about 10% in spite of high temperature at 100°C. In addition, inductance has risen about 30% at normal temperature.
- Using flat-square wire for winding, that is rising space factor, these inductors can reduce current resistance and suppress calorific value.
- Forming internal gap, their structure suppress outgoing magnetic flux leakage.
- Completely Pb free for both inside of products and terminal electrodes.


APPLICATIONS

 Choke coils in power circuit of note book computers, LCD, DVD, STB, PDP, amusement equipment, etc.

SPECIFICATIONS

Operating temperature range	−20 to +105°C	
operating temperature range	[Including self-temperature rise]	
Storage temperature range	-40 to +105°C[Unit of products]	

RECOMMENDED REFLOW SOLDERING CONDITIONS



PRODUCT IDENTIFICATION

RLF	12560	T-	1R0	Ν	140
(1)	(2)	(3)	(4)	(5)	(6)

(1) Series name

(2) Dimensions

12560	12.5×12.8×6.0mm (L×W×T)

(3) Packaging style

Т	Taping(reel)	

(4) Inductance value

1R0	1μΗ	
100	10uH	

(5) Inductance tolerance

M	±20%	
N	±30%	

(6) Rated current


8R2	8.2A	
140	14.4A	

PACKAGING STYLE AND QUANTITIES

Packaging style	Quantity
Taping	500 pieces/reel

Conformity to RoHS Directive: This means that, in conformity with EU Directive 2002/95/EC, lead, cadmium, mercury, hexavalent chromium, and specific bromine-based flame retardants, PBB and PBDE, have not been used, except for exempted applications.

SHAPES AND DIMENSIONS/RECOMMENDED PC BOARD PATTERN




ELECTRICAL CHARACTERISTICS

Inductance Inductance		To at francisco and	DC registeres	Rated current(A)*max.		Part No.
mductance (μH)	tolerance (kHz) (mΩ)±20%	Based on inductance change	Based on temperature rise			
1.0	±30%	100	2.8	18.5	14.4	RLF12560T-1R0N140
1.9	±30%	100	3.6	15.6	12.7	RLF12560T-1R9N120
2.7	±30%	100	4.5	14.4	11.5	RLF12560T-2R7N110
4.2	±30%	100	7.4	10.2	10.0	RLF12560T-4R2N100
5.6	±30%	100	8.5	9.7	9.2	RLF12560T-5R6N9R2
7.8	±30%	100	10.2	8.2	8.4	RLF12560T-7R8N8R2
10	±20%	100	12.4	7.5	7.8	RLF12560T-100M7R5

^{*} Rated current: Value obtained when current flows and the temperature has risen to 40°C or when DC current flows and the nominal value of inductance has fallen by 50%, whichever is smaller.

TYPICAL ELECTRICAL CHARCTERISTICS INDUCTANCE CHANGE vs. DC SUPERPOSITION CHARACTERISTICS



[•] All specifications are subject to change without notice.