

ENGLISH

Datasheet

Stock No: 827-4218

RS Pro SY Control Screened Cable, 7

Core

SY cables are number coded control and connecting cables for flexible use and fixed installation for medium mechanical use. They are for use in dry, damp and wet rooms. They may only be installed outdoors with UV-protection and in observation of the temperature range. At room temperature it is generally resistant against acids, caustics solutions and certain oils. SY cables are used as supply and interconnecting cable for controlling machine tools, production lines, control equipment on conveyors, also for use in measuring regulating and computer units. Suitable for free movement without forced guidance and tensile stress. The braiding of galvanized steel wires are an additional mechanical protection.

Technical Data

Conductor : Bare copper, fine wire strand in accordance to IEC 60 228 that is VDE 0295, class 5

Core insulation : PVC compound TI1 in accordance to VDE 0207

Identification : In acc. to VDE 0293, black cores with white numbers with or without green / yellow ground conductor

Inner sheath : PVC compound TM2 in acc. to VDE 0207

Braid : Galvanised steel wire braid

Outer sheath : Transparent PVC compound TM2 in acc. to VDE 0207

Nominal voltage : 300 / 500 V Test voltage : 3,000 V ac

Temperature range : For flexible use -5 up to +70°C maximum conductor temperature

Fixed installation -40 up to +80°C maximum conductor temperature

Minimum bending radius : Fixed installation 12.5 x cable diameter

Flame retardant : In acc. to IEC 60 332.1 resp. VDE 0472 part 804

EC directive : This cable confirms to ECD 73 / 23 / EEC (low voltage directive)





Specifications:

Description	Number of Cores × Cross Sectional Area (mm²)	Outer Diameter (mm)	Weight Kg / Km
Cable, SY, 3 Core, 2.5 mm, 50M	3 × 2.5	10.6	206
Cable, SY, 4 Core, 2.5 mm, 50M	4 × 2.5	11.5	260
Cable, SY, 5 Core, 2.5 mm, 50M	5 × 2.5	12.6	307
Cable, SY, 7 Core, 2.5 mm, 50M	7 × 2.5	13.9	374
Cable, SY, 3 Core, 0.75 mm, Per M	3 × 0.75	7.9	113
Cable, SY, 4 Core, 0.75 mm, Per M	4 × 0.75	8.5	129
Cable, SY, 5 Core, 0.75 mm, Per M	5 × 0.75	9.2	148
Cable, SY, 7 Core, 0.75 mm, Per M	7 × 0.75	9.9	174
Cable, SY, 3 Core, 1 mm, Per M	3 × 1	8.3	125
Cable, SY, 4 Core, 1 mm, Per M	4 × 1	8.9	145
Cable, SY, 5 Core, 1 mm, Per M	5 × 1	9.6	168
Cable, SY, 7 Core, 1 mm, Per M	7 × 1	10.4	144
Cable, SY, 3 Core, 1.5 mm, Per M	3 × 1.5	9	151
Cable, SY, 4 Core, 1.5 mm, Per M	4 × 1.5	9.7	176
Cable, SY, 5 Core, 1.5 mm, Per M	5 × 1.5	10.6	207
Cable, SY, 7 Core, 1.5 mm, Per M	7 × 1.5	11.5	264
Cable, SY, 3 Core, 2.5 mm, Per M	3 × 2.5	10.6	206
Cable, SY, 4 Core, 2.5 mm, Per M	4 × 2.5	11.5	260
Cable, SY, 5 Core, 2.5 mm, Per M	5 × 2.5	12.6	307