



MOD	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
4	BD	39				U	ADDED -8 NPR 4680 AND REDRAWN ON CAD, OBS -4 EC 0020-344-93	04/06/93	-
						U1	REVISED PER ECO-09-020935	08SEP09	KK AEG



TAPE MTG DETAIL
SCALE 2:1

1. 0.76µm [.000030] MIN GOLD OVER 1.27µm [.000050] MIN NICKEL.
2. 1.27µm [.000050] MIN GOLD OVER 1.27µm [.000050] MIN NICKEL.
3. WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL-
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER-
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4	OBSOLETE	SMALL PACK	1	201568-8
	OBSOLETE	STANDARD	2	201568-4
		TAPE MTG (SEE DETAIL) 3	1	201568-3
		STANDARD	1	201568-1
		PACKAGING TYPE	SOCKET BODY FINISH	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL SOCKET BODY: COPPER ALLOY SPRING: STAINLESS STEEL FINISH SOCKET BODY: SEE TABLE		DR 04/06/93 D.GELTZ CHK 4-26-93 R.STONE APPD 4-29-93 R.S.KLINE APPD - PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	AMP AMP Incorporated Harrisburg, PA 17105-3608 NAME CONTACT ASSEMBLY, SOCKET, #16, 14 AWG, TYPE II SIZE CAGE CODE DRAWING NO C 00779 C-201568 SCALE 10:1 SHEET 1 OF 1	