



Connectors > RF Connectors > Coax Connectors



RF Interface: **Mini UHF**

RF Connector Style: **Plug**

Compatible With RF Cable Type: **KX 15, RG 141A, RG 58C, RG 76, URM 43**

Connector & Contact Terminates To: **Wire & Cable**

Termination Method to Wire & Cable: **Crimp**

Features

Product Type Features

RF Interface	Mini UHF
RF Connector Style	Plug
Compatible With RF Cable Type	KX 15, RG 141A, RG 58C, RG 76, URM 43
Connector & Contact Terminates To	Wire & Cable

Body Features

Body Material	Zinc
Body Plating Material	Nickel

Contact Features

Crimp Type	Single Crimp
RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Dielectric Material	Delrin
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2020 (205) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #430079-000  
7528A5314-0




TE Part #165805-000  
D-602-0144




TE Part #293973-000  
TXR40AB00-1612AI




TE Part #658819-000  
TXR40AB00-1006AI




TE Part #554173-000  
TXR40AB00-1406AI




TE Part #806677-000  
214A032-25-0



TE Part #900469-000  
RBD-50-M-00



TE Part #980286-000  
242W042-25-0



Documents

Product Drawings

M-UHF Str Plg Hex Nickel Pltd RG58C/U

English