

INSTA CONTACTOR 0/1 AUTOMATIC WITH 1 NO CONT. AND 1 NC CONT. CONTACT FOR AC 230, 400V 20A ACTIVATION ACDC24V



Model	
Product brand name	SETRON
Product designation	Insta contactors
Design of the product	1 NO contact 1 NC contact
Type of voltage / of the operating voltage	AC
Type of voltage / for actuation	AC/DC
Protection class	
Protection class IP	IP20
Dissipation	
Power loss [W]	
<ul style="list-style-type: none"> for rated value of the current / at AC / in hot operating state / per pole 	1.7 W
<ul style="list-style-type: none"> maximum 	1.7 W
Main circuit	
Operating voltage / rated value	
<ul style="list-style-type: none"> minimum 	230 V
<ul style="list-style-type: none"> maximum 	230 V
Operating current / rated value	20 A

Control current

Control supply voltage

- | | |
|-------------------------|------|
| • rated value | 24 V |
| • rated value / maximum | 24 V |
| • at DC / rated value | 24 V |

Product details

Product component / Slide for manual operation Yes

Product extension / can be installed / supplementary devices Yes

Number

Number of NC contacts 1

Number of NO contacts 1

Mechanical Design

Height 90 mm

Width 17.5 mm

Depth 71 mm

Installation depth 64 mm

Number of width units 1

Net weight 150 g

Certificates

Equipment marking / acc. to DIN EN 61346-2 Q

General Product Approval

Declaration of Conformity



CCC



UL

[Miscellaneous](#)



EG-Konf.

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5TT5001-8>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5TT5001-8>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5TT5001-8

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



-K

