


Device marker - EMLP-AL (85,6X54) CUS - 0830522

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Device marker, can be ordered: Piece, aluminum, labeled according to customer specifications, Mounting type: Adhesive, Lettering field: 85.6 x 54 mm



Key commercial data

Packing unit	1
GTIN	 4 046356 718646
Custom tariff number	76169990

Technical data

Dimensions

Length (b)	85.6 mm
Width (a)	54 mm

Ambient conditions

Recommended storage conditions	-25 °C to +120 °C (>+80 °C slight changes of the material surface possible)
--------------------------------	---

General

Color	aluminum
Components	free from silicone, halogen, and cadmium
Material	Aluminum
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	1
Number of individual labels per row	1
Adhesive	Acrylic
Printability	UV LED technologie
Device	5147999 BLUEMARK CLED
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03

Device marker - EMLP-AL (85,6X54) CUS - 0830522

Technical data

General

Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	Adhesive

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410