


# Geberit Mapress Stainless Steel adaptor with union nut made of CrNi steel



Example image

## APPLICATION PURPOSES

- For cold and hot potable water
- For cooling and heating water without antifreeze agent
- For cooling and heating water with antifreeze agent
- For district heating water ≤ 120 °C
- For saturated steam ≤ 120 °C
- For service water and process water
- For treated water
- For rainwater with a pH value ≥ 5.5
- For grey and black water with a pH value ≥ 5.5
- For extinguishing water (wet)
- For extinguishing water (wet/dry, dry)
- For sprinklers (wet)
- For chemicals and technical liquids
- For compressed air (oil purity class 0–3)
- For negative pressure
- For inert gases (e.g. nitrogen)
- For industrial gases (e.g. acetylene, shielding gases)
- Suitable exclusively for threads with an inner diameter of ≤ di, see table
- For technical building systems, industry and shipbuilding

## CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Seal ring made of CIIR, black
- Flat gasket made of EPDM
- Pressing socket with transparent protection plug

## TECHNICAL DATA

|                                          |                                |
|------------------------------------------|--------------------------------|
| Medium temperature with flat gasket EPDM | 0–100 °C                       |
| Product material                         | CrNiMo steel 1.4401 (EN 10088) |

| Art. no. | DN | d, ø mm | G " | di, ø mm | L cm | Z cm |
|----------|----|---------|-----|----------|------|------|
| 35132    | 12 | 15      | 3/4 | 13       | 3.7  | 1.1  |
| 35134    | 20 | 22      | 1   | 20       | 4    | 1.1  |

| Art. no. | DN | d, ø<br>mm | G<br>" | di, ø<br>mm | L<br>cm | Z<br>cm |
|----------|----|------------|--------|-------------|---------|---------|
| 35075    | 25 | 28         | 1 1/2  | 32          | 4.4     | 1.3     |