

## Features

- Thermoresistances
- Max. operating temperature 400°C
- ½" fittingnut
- Protection tube AISI304 (DIN1.4301)
- Sensor type DIN/EN60751
- Cable type Fiber glass+Fiber glass+Braided
- Immersion Length 50mm
- Cable Length: 1m

## RS PRO Bayonet Type Fittingnut PT-100 Thermoresistances With ½" fittingnut

RS Stock No.: 0350418



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Standard Bayonet Type PT100 Thermoresistances Temperature Sensor

Diameter(M): 6mm

Immersion Length(L): 50mm

Cable Length(K): 1m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


## General Specifications

Max. Operating Temperature	-50 °C / +400 °C
Standard cable types	Fiber glass + fiber glass + braided wire
Sensor type	DIN/EN60751 Class "B"
Protection tube material	AISI304 (DIN1.4301) Standard production
Connector	½" fittingnut

## Mechanical Specifications

Diameter (M)	6mm
Immersion Length (L)	50mm
Cable Length (K)	1m

## Electrical Connection



### PT-100 Connections

