Parker Product Datasheet



This range of ergonomic polymer couplers has been designed for the safety of operators and machinery while giving very high energy efficiency performance.
Available in three profile standards, it is perfectly suited for any type of installation.

PART NUMBER: 9401E07 17
COUPLING HALF: Coupler
CONNECTION SIZE: G 3/8
SLEEVE MATERIAL: Thecnical polymer
BODY MATERIAL: Brass
CONNECTION TYPE: Male BSPP
DIAMETER: ND 7.2
PROFILE: EURO

PRODUCT OVERVIEW

This range of ergonomic polymer couplers has been designed for the safety of operators and machinery while giving very high energy efficiency performance.

Available in three profile standards, it is perfectly suited for any type of installation.

Features/Benefits:

- Safety & Reliability

• Prevents risk of whiplash
• Quick-acting vent allowing disconnection to be carried out in total safety

• Rotating sleeve to avoid risk of accidental disconnection
• Low connection/disconnection force even under pressure
• Polymer sleeve protects equipment from scratching
• Protective spiral over the tube prevents kinking

- Performance

• Very high flow and low pressure drop
• 100% leak-tested in production
• Date coding to guarantee quality and traceability
• Robust impact-resistant material
• Optimum energy efficiency
• Long-term reliability

- Easy-to-Use

• Immediate identification by clear marking on each model showing:
profile of the compatible male probe
type part number
• Compatible with male probes conforming to:
ISO B profile
European profile
ARO profile

Markets:

• Packaging
• Miscellaneous Manufacturing
• Vehicle Assembly Facilities

Applications:

• Compressed Air Circuits Automatic Connection and Disconnection
• Workshops
• Air Operated Tools
• Ring Main Circuits
• Cleaning
• Blowing

Technologies:

• Quick acting coupler
• Quick coupling
• Quick connect coupling
• Quick connect coupler
• Y coupler
• Coupler
• Coupling
• C9000

Technical Characteristics:

• Compatible fluids: Compressed air
• Materials: Technical polymer, aluminium, nickel-plated brass, zamak, stainless steel
• Pressure: Vacuum to 16 bar
• Temperature: -20°C to +60°C

Regulations:

• DI: 97/23/EC (PED)
• DI: 2002/95/EC (RoHS), 2011/65/EC
• DI: 1907/2006 (REACH)
• ISO 4414 Pneumatic Fluid Power: General Rules Relating to Systems
• DIN EN 983 Safety Standard for Pneumatics

Product Types:

• Coupler, Male BSPP Thread
• Coupler, Male BSPT Thread
• Coupler, Female BSPP Thread
• Coupler, LF 3000® Push-In Connection, Body Spiral Protection Spring
• Coupler with Hosetail
• Coupler, Bulkhead Mountable, Female BSPP Thread
• Y Coupler, Female BSPP Thread
• Probe, Straight-Through, Male BSPP Thread
• Probe, Straight-Through, Female BSPP Thread
• Probe, Straight-Through, LF 3000® Push-In Connection, with Spiral Protection Spring
• Probe, Straight-Through, with Hosetail
• Coupler, Male BSPP Thread
• Coupler, Female BSPP Thread

- Coupler, LF 3000® Push-In Connection, with Spiral Protection Spring
- Coupler with Hosetail
- Coupler, Bulkhead Mountable, Female BSPP Thread
- Y Coupler, Female BSPP Thread
- Probe, Straight-Through, Male BSPP Thread
- Probe, Straight-Through, Female BSPP Thread
- Probe, Straight-Through, LF 3000® Push-In Connection, with Spiral Protection Spring
- Probe, Straight-Through, with Hosetail
- Coupler, Male BSPP Thread
- Coupler, Male BSPT Thread
- Coupler, Female BSPP Thread
- Coupler, LF 3000® Push-In Connection, with Spiral Protection Spring
- Coupler, Bulkhead Mountable, Female BSPP Thread
- Y Coupler, Female BSPP Thread
- Probe, Straight-Through, Male BSPP Thread
- Probe, Straight-Through, Female BSPP Thread
- Probe, Straight-Through, Male BSPT Thread
- Probe, Straight-Through, LF 3000® Push-In Connection, with Spiral Protection Spring
- Probe, Straight-Through, with Hosetail

TECH SPECIFICATIONS

QUANTITY PER BOX	5
FUNCTION	Self-Venting
CONNECTION TYPE	BSPP
BRAND	Parker
INTERCHANGE TYPE	European Profile
COUPLING HALF	Coupler
BRAND	Legris
SEAL MATERIAL	NBR
FOR FLUID TYPE	Air & Neutral Gases (Industrial compressed, lubricated air, inert gases)
MAXIMUM OPERATING TEMPERATURE	140 °F

OPERATION TYPE	Rotative Sleeve
CONNECTION SIZE	G 3/8
FLOW RATE	2000 L/min (air)
MINIMUM OPERATING TEMPERATURE	-4 °F
DIVISION	Low Pressure Connectors Europe Division
CONNECTION TYPE	Male
DIAMETER	7.2 mm (nominal)
PLATING TYPE	Nickel-Plated
PRODUCT SERIES	Series C9000
TECHNOLOGY	Pneumatics
BODY MATERIAL	Brass
COMPATIBLE FITTING	C9000 Plug
VALVE INCLUDED	Yes
INDUSTRY	Industrial Manufacturing Equipment
PRODUCT TYPE	Quick Coupling
SLEEVE MATERIAL	Technical Polymer
COMPATIBLE FITTING	Series 25 Plug
MAXIMUM OPERATING PRESSURE	233 psi
MINIMUM OPERATING TEMPERATURE	-20 °C
APPLICATION	Workshops, Cleaning, Blowing, Pneumatics, Air-Operated Tools, Ring Main Circuits, Packaging
MAXIMUM OPERATING TEMPERATURE	60 °C
MAXIMUM OPERATING PRESSURE	16 bar
DIVISION	Low Pressure Connectors Europe Division
WEIGHT	0.122 kg