

Part No. X1005249-LGA2SA10A2 GPS/GLONASS (active) & LTE 2-in-1 External Antenna

(1575 / 1602) MHz + (698-960; 1710-2170; 2300-2690) MHz

Supports: Tracking, Smart Home, Agriculture, Automotive Aftermarket, Healthcare, Digital Signage, Logistics, Industrial Devices



GPS/GLONASS (active) & LTE External Antenna

(1575 / 1602) MHz (698-960; 1710-2170; 2300-2690) MHz

KEY BENEFITS

Reduced Costs and Time-to Market

Standard antennas eliminate design fees and cycle time associated with a custom solution. getting products to market faster.

High Performance

By optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily met. Reliability

Products are the latest RoHS & REACH version compliant.

APPLICATIONS

Remote Monitoring
Point of Sale
IoT devices
Gateway
Telematics
Tracking
Healthcare M2M, Industrial devices
Smart Grid
Logistics
Energy
Retail

Ethertronics' 2-in-1 GPS/GLONASS (active) and LTE external antenna delivers on the key needs of device designers for higher functionality and performance.

Electrical Specifications

Frequency (GPS-GLONASS)	1575 MHz	1602 MHz				
Gain at Zenith	3.0 dBi	3.5 dBi				
VSWR	2.0:1 max					
Impedance	50 Ω					
LNA Electrical Properties						
Frequency (GPS/GLONASS)	1575 MHz	1602 MHz				
VSWR	2.0:1 max					
Impedance	50 Ω					
Antenna Gain (@3.3 V)	28 dB / 25 dB min.					
DC Power Input	3~5 V					
Noise Figure	2.5 dB Typ.					
Power Consumption (@ 3.3 v)	9 mA Typ.					

Frequency (LTE)	698~960 MHz	1710~2170 MHz	2300~2690 MHz		
Peak Gain	3.7 dBi	3.6 dBi	3.6 dBi		
Average Efficiency	40%	57%	55%		
VSWR	5.0:1 max	3.8:1 max	2.3:1 max		
Impedance		50 Ω			




Mechanical Specifications

Ordering Part #	X1005249-LGA2SA10A2	
Dimensions (mm)	55.0 x 55.0 x 20.0	
Mounting Type	Foam Adhesive	
Operating Temperature °C	-40 ~ +85	
Housing Material & Color	PC+ABS (Black)	
Weight (grams)	112	
Cable	Length: 1M Type: RG-174 GPS-GLONASS CFD-200 LTE	
Connector	GPS-GLONASS SMA(M) LTE SMA(M)	
Waterproof	IPX5	

VSWR Plots (GPS/GLONASS 1575 &1602 MHz)

Typical characteristics in free-space

VSWR:







VSWR, Efficiency Plots (LTE 698-2690 MHz)

Typical characteristics in free-space

VSWR:



Efficiency:






Peak Gain Plots (LTE 698-2690 MHz)

Typical characteristics in free-space


Peak Gain:






2D Radiation Patterns (LTE 698-960 MHz)











2D Radiation Patterns (LTE 1710-2170 MHz)











2D Radiation Patterns (LTE 2300-2690 MHz)










Mechanical Dimensions

Typical antenna dimensions (mm)

Part Number	A (mm)	B (mm)	C (mm)	D (mm)
X1005249-LGA2SA10A2	55.0 ± 1.0	55.0 ± 1.0	20.0 ± 0.5	1000 ± 40.0



Side View



Bottom View

