




Passive Components > Resistors > Chassis Mount Resistors > Power Wirewound Resistor: Mineral, CFH



Resistor Type: **Power Resistor**

Resistance Class: **Up to 1k Ω**

Resistance Value: **3.3 Ω**

Power Rating: **750 W**

Element Type: **Wire Wound**

[All Power Wirewound Resistor: Mineral, CFH \(17\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Wire Wound

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Operating Voltage	1500 V
Resistance Class	Up to 1k Ω
Resistance Value	3.3 Ω
Power Rating	750 W
Passive Component Tolerance	5 %

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	Flying Leads

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Slots
--------------------------	----------------------------

Dimensions

--



Product Height	30 mm[1.181 in]
Product Length	110 mm[4.331 in]
Product Width	95 mm[3.74 in]

Packaging Features

Packaging Method	Loose Piece - Box
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

CFH350A3R3J

3.3 ohm Chassis Mount Resistor, 750 W, Wire Wound, 2 Terminations, 5 %, Flying Leads, Loose Piece - Box, 30 mm [1.181 in] Height, CGS CFH



TE Part # 2-1623821-8
CFH 1100 120R 5% 300MM LEADS

TE Part # 2-1623821-7
CFH350 620R 5% 1000MM LEADS

TE Part # CAT-C339-C339
Power Wirewound Resistor: Mineral, CFH

Also in the Series | CGS CFH

Chassis Mount Resistors(21)

Customers Also Bought

TE Part #3-644488-3
13P MTA100 SHRD HDR F/L R/A SN

TE Part #720788-8
EXTRCTION TOOL FOR MINI SPRING

TE Part #NB-PTCO-166
Pt100, 2.0x5.0, Class C, PTFD101C1A0

TE Part #9-2176414-1
7W STD M/OX 5% 110K

TE Part #2307725-8
8P,2MM,B-B,REC,SRHZ,SMD,0.1AU,TR

TE Part #T4151210004-003
RPC-M12-MR-4CON-PVC-1.5

TE Part #1623804-3
SQZ10 3R9 5% WIRE

TE Part #4-87348-0
40 MODII HDR SRST UNSHRD .100

TE Part #1-2319764-3
E STACK PIANO 6P G LONG TUBE PD OFF

TE Part #1558666-6
T9GS1L14-22



Documents

Product Drawings

CFH 350 3R3 5% 300MM LEADS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1623821-9_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1623821-9_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1623821-9_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English

Aluminium_Housed_Power_Resistors-Type_CFH_Series

English