

## FEATURES

- **Graphite and PTFE material:** Provides excellent thermal and chemical resistance, ensuring durability in harsh environments
- **Maximum operating pressure of 8500 kPa:** Suitable for high-pressure applications, enhancing safety and reliability
- **Maximum operating temperature of 280 °C:** Capable of withstanding extreme temperatures, offering versatility across various applications
- **Rotary speed of 28 m/s:** Supports high-speed operations, ensuring efficient performance
- **8mm section:** Ideal for precise sealing requirements, improving installation efficiency

## RS PRO 8mm Gland & Valve Packing, 8m Length

RS Stock No: 606-564



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO gland and valve packing is designed for sealing applications in industrial environments. Made from a combination of graphite and polytetrafluoroethylene, it offers excellent resistance to high temperatures and pressures, making it ideal for demanding conditions. Its primary benefit is ensuring reliable sealing performance, reducing maintenance needs and downtime.

## General Specifications

Maximum Operating Pressure	8500 kPa
Product Type	Gland & Valve Packing
Rotary Speed	28 m/s
Section	8 mm
Sub Type	Gland Packing

## Mechanical Specifications

Length	8 m
Material	Graphite, Polytetrafluoroethylene

## Operation Environment Specifications

Maximum Operating Temperature	280 °C
-------------------------------	--------

## Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, RoHS
---------------------	----------------------------