


Geberit Mapress Stainless Steel T-piece, reduced (gas)



Example image



APPLICATION PURPOSES

- For natural gases
- For liquefied gases
- For biogases
- For natural and liquefied gases

CHARACTERISTICS

- Pressing indicator
- Leaky if unpressed
- Marked in yellow
- Seal ring made of HNBR, yellow

- LABS-free
- Pressing socket with yellow protection plug

TECHNICAL DATA

Product material CrNiMo steel 1.4401 (EN 10088)

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	I2 cm	Z cm	Z1 cm	Z2 cm
34035	15 / 12 / 15	18	15	18	90	6.8	4.1	3.4	3.4	1.4	2.1	1.4
34036	20 / 12 / 20	22	15	22	90	7.4	4.3	3.7	3.7	1.6	2.3	1.6
34037	20 / 15 / 20	22	18	22	90	7.4	4.3	3.7	3.7	1.6	2.3	1.6
34038	25 / 12 / 25	28	15	28	90	8.4	4.6	4.2	4.2	1.9	2.6	1.9
34039	25 / 15 / 25	28	18	28	90	8.4	4.6	4.2	4.2	1.9	2.6	1.9

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
34040	25 / 20 / 25	28	22	28	90	8.4	4.7	4.2	4.2	1.9	2.6	1.9
34041	32 / 12 / 32	35	15	35	90	10	4.9	5	5	2.4	2.9	2.4
34042	32 / 15 / 32	35	18	35	90	10	4.9	5	5	2.4	2.9	2.4
34043	32 / 20 / 32	35	22	35	90	10	5	5	5	2.4	2.9	2.4
34044	32 / 25 / 32	35	28	35	90	10	5.3	5	5	2.4	3	2.4
34140	40 / 12 / 40	42	15	42	90	11.4	5.3	5.7	5.7	2.7	3.3	2.7
34141	40 / 15 / 40	42	18	42	90	11.4	5.3	5.7	5.7	2.7	3.3	2.7
34045	40 / 20 / 40	42	22	42	90	11.4	5.4	5.7	5.7	2.7	3.3	2.7
34046	40 / 25 / 40	42	28	42	90	11.4	5.7	5.7	5.7	2.7	3.4	2.7
34047	40 / 32 / 40	42	35	42	90	11.4	6.1	5.7	5.7	2.7	3.5	2.7
34048	50 / 20 / 50	54	22	54	90	13.8	6	6.9	6.9	3.4	3.9	3.4
34049	50 / 25 / 50	54	28	54	90	13.8	6.3	6.9	6.9	3.4	4	3.4
34050	50 / 32 / 50	54	35	54	90	13.8	6.7	6.9	6.9	3.4	4.1	3.4

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	I2 cm	Z cm	Z1 cm	Z2 cm
34051	50 / 40 / 50	54	42	54	90	13.8	7.1	6.9	6.9	3.4	4.1	3.4
34062	65 / 20 / 65	76.1	22	76.1	90	23	7.2	11.5	11.5	6.2	5.1	6.2
34065	65 / 25 / 65	76.1	28	76.1	90	23	7.5	11.5	11.5	6.2	5.2	6.2
34079	65 / 32 / 65	76.1	35	76.1	90	23	7.9	11.5	11.5	6.2	5.3	6.2
34080	65 / 40 / 65	76.1	42	76.1	90	23	8.3	11.5	11.5	6.2	5.3	6.2
34097	65 / 50 / 65	76.1	54	76.1	90	23	8.9	11.5	11.5	6.2	5.4	6.2
34081	80 / 20 / 80	88.9	22	88.9	90	26	7.8	13	13	7	5.7	7
34082	80 / 25 / 80	88.9	28	88.9	90	26	8.1	13	13	7	5.8	7
34085	80 / 32 / 80	88.9	35	88.9	90	26	8.5	13	13	7	5.9	7
34088	80 / 40 / 80	88.9	42	88.9	90	26	8.9	13	13	7	5.9	7
34098	80 / 50 / 80	88.9	54	88.9	90	26	9.5	13	13	7	6	7
34094	100 / 20 / 100	108	22	108	90	31	8.8	15.5	15.5	8	6.7	8
34095	100 / 25 / 100	108	28	108	90	31	9.1	15.5	15.5	8	6.8	8

Art. no.	DN	d, ø mm	d1, ø mm	d2, ø mm	arc °	L cm	L1 cm	I cm	l2 cm	z cm	z1 cm	z2 cm
34096	100 / 32 / 100	108	35	108	90	31	9.5	15.5	15.5	8	6.9	8
34125	100 / 40 / 100	108	42	108	90	31	9.9	15.5	15.5	8	6.9	8
34099	100 / 50 / 100	108	54	108	90	31	10.5	15.5	15.5	8	7	8