



RJ45 ICM 1G Base-T Vertical

Part No:

TMJD4835-8KB51NL

Description:

RJ45 connector with integrated magnetics 1G Base-T

Vertical with THT mount and LED (Green/Yellow, Yellow/Green)

Features:

Vertical

Shielded

Long face

Transformer + CMC

8 cores per Jack

Board Lock

Industrial grade



-	1.	Introduction	3
2	2.	Specifications	4
3	3.	Mechanical	5
4	4.	Electrical	7
į	5.	Packaging	8
		Changelog	9

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.













1. Introduction



The Taoglas TMJD4835-8KB51NL is a vertical RJ45 Integrated Connector with a shielded body design. It features a widely recognized footprint and a compatible package that aligns with industry standards for RJ45 Integrated Connectors, making it popular among users. This connector supports 1G Base-T connections.

Typical Applications Include:

- Industrial Automation
- Hubs
- Routers
- Switches
- Wireless Access Points

Taoglas Magnetics offer an extensive product line of RJ45 Integrated Connectors designed for commercial and industrial grade applications, supporting 10/100 Base-T (Atmos100 Series) and 1G Base-T (Atmos1000 series). These surface mount or through-hole components provide reliable performance and maintain signal integrity that meets IEEE 802.3 standards, and they are UL certified. The Power over Ethernet options are also available including PoE, PoE+ and PoE++.

The majority of Taoglas RJ45 ICMs are manufactured with fully automated winding, assembly & testing to ensure consistent performance, quality and reliability while ensuring cost competitiveness for its customers. These products are fully compliant with the REACH and RoHS directive, and compatible with all major PHY vendors.

For customized products or support with integration, contact your regional Taoglas customer support team for further information.



2. Specifications

Electrical Performance @25°C			
Inductance	350μH Min @100KHz,0.1V, 8mA DC Bias		
Turns Ratio (±3%)	1CT:1CT		
Insertion Loss	-1.1dB MAX @ 1MHz TO 100MHz		
Return Loss (100 OHMS ±15%)	-18dB MIN @ 1MHz TO 40MHz		
	-14dB MIN @ 60MHz		
	-12dB MIN @ 80MHz		
	-10dB MIN @ 100MHz		
Cross talk	-35dB MIN @ 1MHz TO 10MHz		
	-26dB MIN @ 15MHz TO 60MHz		
	-24dB MIN @ 60MHz TO 100MHz		
CM TO CM REJ	-35dB MIN @ 1MHz TO 60MHz		
	-30dB MIN @ 60MHz TO 100MHz		
Isolation PHY SIDE To Line SIDE	1500Vrms		

Environmental Specifications				
Operating Temperature	-40°C TO +85°C			

Material Specifications			
Housing	Thermoplastic PBT+30%G.F UL94V-0		
Contact	Phosphor Bronze C5210R-EH Thickness=0.35mm		
Pins	Brass C2680R-H Thickness=0.35mm		
Shield	Copper alloy Brass H65Y Thickness=0.2mm		
Contact Plating	Gold 30 micro-inches min. in contact area		
Wave solder tip temperature	250°C, 5 Sec		


Compliance		
IEEE 802.3		
RoHS Compliant		


Storage requirements			
Humidity	MSL - 1		
Storage Temperature	-40°C TO +85°C		



3. Mechanical

3.1 Mechanical Drawings






Mechanical Specifications				
Height	16.76 mm			
Width	16.10 mm			
Depth	23.15 mm			
Weight	7.6 g			
Mounting Style	Through Hole (THT)			
Mounting Angle	Vertical			





3.2 PCB Layout




 $\label{eq:Suggested PCB Layout (Top View)}$ Dimensions are in millimeters with the following tolerances: X.XX = ± 0.10




6


4. Electrical

4.1 Electrical Drawings




4.2 LED





Emitting Color	λp(nm)	VF@IF=20mA	IR @VR=5V
GREEN	565	1.8~2.6V	10 µA max
YELLOW	585	1.8~2.6V	10 µA max

4.3 Profile of Wave Solder






5. Packaging

SPQ

1 tray = 40 pcs

Tray size = 294x154x24.5mm

Tray Weight = 0.344kg




Carton

1 Carton = 18 trays = 720 pcs

Carton dimensions = 370*300*300 mm

Carton Weight = 7.5 kg



Label

Taoglas Limited

P/N NO: XXXXXXXX

QYT: XXX PCS DC: XXXX

DATE: XXXX-XX-XX

SPQ Label (8x4cm)

Taoglas Limited

P/N NO: XXXXXXXX

PO: XXXXXXXX B/N: XXXXXXXX

QYT: XXX PCS DC: XXXX


DATE: XXXX-XX-XX

Carton Label (8x4cm)

www.taoglas.com SPE-24-8-097-A



Changelog







www.taoglas.com

