




Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Male Screwlock**
Primary Product Material: **Stainless Steel, Zinc Alloy**
Operating Temperature (Max): **150 °C [302 °F]**
Operating Temperature Range: **-55 – 150 °C [-67 – 302 °F]**
Hardware Accessory Function: **Latching, Locking & Retention**

Features

Product Type Features

Connector Hardware Accessory Type	Male Screwlock
Hardware Accessory Function	Latching, Locking & Retention

Body Features

Primary Product Material	Stainless Steel, Zinc Alloy
--------------------------	-----------------------------

Mechanical Attachment

Hardware Type Included	Jackscrew Tip Female and Spirol Pin
Thread Size	6-32
Product Plating Finish	Chromate

Dimensions

Product Width	7.92 mm[.312 in]
Product Length	68.66 mm[2.703 in]
Product Height	7.92 mm[.312 in]

Usage Conditions

Operating Temperature (Max)	150 °C[302 °F]
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]



Packaging Features

Packaging Method	Bag
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 201501-1
SPIROL PIN



TE Part # 201910-1
JACKSCREW KIT



Also in the Series

AMP M Series

Board-to-Board Jumpers & Shunts(5)	Connector Contacts(51)	Connector Hardware(46)	Power Contacts(51)
Rectangular Connector Housings(77)	Rectangular Power Connectors(82)	Standard Rectangular Connectors(81)	

Customers Also Bought

TE Part #52453-1 PG SPR SPD 22-16COMM22-18MIL 6	TE Part #31818 SPLICE, SOLIS, BUTT, 22-16 COMM 22-18MIL	TE Part #640903-2 RECEPT,PIDG FASTON 22-18 250	TE Part #42110-3 RING TERMINAL 18-14 AWG BR
TE Part #859113-1 SOCKET & BUSHING ASSY	TE Part #52465-1 TERMINAL,PG SPR SPD 16-14 10	TE Part #201047-2 SERIES "M" ST. STL. GUIDE SOC.	TE Part #1-201046-2 SERIES "M" MIN RECT GUIDE PIN
TE Part #2-34855-1 TERMINAL,PG R 12-10 1/4	TE Part #52430-2 TERMINAL,PIDG SPR SPD 12-10 6		



Documents

Product Drawings

JACKSCREW KIT

English

CAD Files

Customer View Model

ENG_CVM_201911-1_J1.3d_igs.zip

English

Customer View Model

ENG_CVM_201911-1_J1.3d_stp.zip

English

Customer View Model

ENG_CVM_201911-1_J1.2d_dxf.zip

English

3D PDF

English

Customer View Model

ENG_CVM_CVM_201911-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_201911-1_D.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_201911-1_D.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Instruction Sheets

Instruction Sheet (U.S.)

English

AMP TURNABLE JACK SCREW SPECIFICATIONS AND ASSEMBLY INSTRUCTIONS

English