

Nibbler LXT®

DJN161

18V • 1 900 min⁻¹

Clean and precise cutting of metal and other sheets

A slimline nibbler with a 18V LXT® battery that achieves precise arced and straight cuts cleanly. Ideal for cutting profile sheets, such as roofing materials. The nibbler die rotates 360 degrees. A cutting capacity of 2.5 mm for aluminium and 1.6 mm for steel.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Strokes per Minute (SPM)	1900 min ⁻¹
Min. Internal Cutting Radius	45 mm
Cutting Capacity Aluminium (Up To 200N/mm ²)	2,5 mm
Cutting Capacity Mild Steel (up to 400N/mm ²)	1,6 mm
Cutting Capacity Stainless Steel (up to 600N/mm ²)	1,2 mm
Sound Pressure Level (L _{pA})	93 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Cutting Sheet Metal	6,5 m/s ²
Tool weight with battery	1,9 - 2,3 kg
Product Dimensions (L x W x H):	313 x 78 x 189 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits

- Slim body design for a good grip
- Electronic overload protection protects the user and the device
- Anti-restart function minimises accidental start-up
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Optional AC

762013-6

Thickness Gauge 0,5 / 1,0 / 1,5 mm



783208-8

Hex Wrench 2,5 mm



821551-8

Makpac case (3)



837678-4

MakPac (3) Inlay



A-15051

Die



A-83951

Nibbler, Punch



Other

User manual

Parts drawing